

6ft Swivel HDMI Cable, 4K High Speed Rotating HDMI Cord, 4K 30Hz UHD HDMI, 10.2 Gbps, HDMI 1.4 Video, HDCP 1.4, M/M Pivot Cable with 180 Swivel Connector, HDMI to HDMI Cable

Product ID: HDMIROTMM6



The HDMIROTMM6 High Speed HDMI Swivel Cable (6 ft) features two gold plated 180 flexible HDMI connectors, which provide a direct link between HDMI-enabled devices such as Blu-Ray players, HDTVs, DVD Players, stereo receivers and more.

The swiveling/pivoting HDMI connectors offer the ability to adjust your installations in tight/narrow spaces where standard connectors will not fit (e.g. wall-mounted flat panel televisions), without having to bend the cable at sharp angles.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

The HDMIROTMM6 6-foot HDMI cable is backed by StarTech.com's Lifetime Warranty.

About StarTech.com HDMI to HDMI Cables:

StarTech.com High Speed HDMI digital video and audio cables are expertly designed and constructed of only top quality materials to ensure high quality, high definition performance. The HDMI standard combines high bandwidth video and multi-channel digital audio into a single cable, and provides crystal clear image resolution.

Certifications, Reports and Compatibility



Applications

- Connecting your HDMI-capable TV or Monitor to an audio-video source which incorporates HDMI technology
- Connecting to an HDMI-enabled A/V source with very little space near the connection point

Features

- **HIGH SPEED SWIVEL CABLE:** 6 ft (1.83 m) HDMI 1.4b cable supports 4K (3840x2160p, 24, 25, 30Hz 4096x2160p, 24Hz), Full HD (1920x1080p, 120Hz), 10.2 Gbps bandwidth, wide aspect ratio, 8Ch Audio (5.1/7.1/DD+/Dolby TrueHD), 3D Video
- **DURABLE:** HDMI Ultra HD cable with pivoting/swiveling/rotating connectors that rotate up to 180, helping installation in narrow spaces or tight angles such as behind wall mounted TV; Long lasting molded PVC connectors; Ideal for Commercial environments
- **QUALITY CONSTRUCTION:** 28AWG wire, corrosion resistant gold-plated connectors, and superior EMI shielding with AI-Mylar foil and braid improve signal integrity and reliability, providing higher quality video and audio
- **APPLICATIONS:** Use in home offices/boardrooms/conference rooms/offices/classrooms, works with your laptop/professional workstation/soundbar for presentations via UHD/4K monitors, projector or large display; Samsung/Sony/Apple TV/Dell/Lenovo
- **SPECS:** 6 ft (1.83 m) Black HDMI 1.4 HDMI Male to Male 28 AWG PVC Jacket Shield: AI-Mylar foil with Braid ARC, Deep Color, HDCP 1.4, CEC, YCC601 Color Supports HDMI 1.4 and earlier

Hardware

Warranty	Lifetime
Number of Conductors	19
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)

Performance

Maximum Digital Resolutions	4K x 2K @ 30 Hz
-----------------------------	-----------------

Connector(s)

Connector A	1 - HDMI (19 pin)
Connector B	1 - HDMI (19 pin)

Physical

Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	6.0 ft [1.8 m]
Cable OD	0.3 in [7.3 mm]
Product Length	6.0 ft [1.8 m]
Weight of Product	4.3 oz [123 g]

Packaging Information

Package Quantity	1
Package Length	4.3 in [10.9 cm]
Package Width	0.8 in [20 mm]
Package Height	8.3 in [21 cm]
Shipping (Package) Weight	4.4 oz [124 g]

What's in the Box

Included in Package	1 - 6 ft 180 Rotating High Speed HDMI Cable - HDMI - M/M
---------------------	--

****Product appearance and specifications are subject to change without notice.***