

33ft (10m) Active HDMI Cable - 4K High Speed HDMI Cable with Ethernet - CL2 Rated for In-Wall Install - 4K 30Hz Video - HDMI 1.4 Cord - For HDMI Monitor, Projector, TV, Display, REPLACED BY HD2MM10MA

Product ID: HDMM10MA



The HDMM10MA 33 ft Active High Speed HDMI Cable features a built-in active signal booster for a connection distance of up to 33 feet (10m) between your HDMI-enabled devices, with no signal loss.

This durable yet lightweight cable features thinner HDMI wire construction that allows for a more flexible installation with minimal clutter. Plus, the cable features built-in amplifier circuitry which actively boosts the HDMI signal with no external power required.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

This 10 meter HDMI cable is backed by StarTech.com's 2-year Warranty.

Please Note: This cable features unidirectional architecture which requires that the cable is installed in the correct direction. Please refer to the "source" and "display" labels on the HDMI connectors in order to ensure that the device and the HDMI source are connected properly.

Certifications, Reports and Compatibility



Applications

- Connecting high-definition A/V devices such as Blu-Ray Disc players, HDTVs, DVD Players, DVRs, game consoles,

projectors etc., over long distances, with no signal loss

Features

- **HIGH SPEED HDMI CABLE:** 32.8 ft (10m) Active HDMI Cable with Ethernet supports 4K Ultra HD video (3840x2160p, 24, 30Hz 4096x2160p, 24Hz), Full HD (1080p 120Hz) HDMI 1.4b wide aspect ratio, 8Ch Audio (5.1/7.1/DD+/Dolby TrueHD), 3D Video
- **ACTIVE CIRCUITRY:** Active bus powered amplifier boosts video signals over longer distances to extend HDMI signal up to 32.8 ft (10 m) (no external power supply needed), supports additional color spaces such as Adobe RGB and YCC601 Color
- **DURABLE CABLE:** Ideal for in-wall installations where CL2 rating is required; Flexible PVC jacket; Al-Mylar Foil with Braid shield & gold plated connectors with metal shell improve signal integrity & block external Electromagnetic Interference (EMI)
- **APPLICATIONS:** Use this long HDMI cable for home office, conference room, office or classroom; works w/ your laptop/professional workstation/soundbar for presentations via UHD/4K monitors, projectors/large HDTV displays; Samsung/Sony/Apple TV/Dell/Lenovo
- **SPECS:** 32.8 feet (10 meters) Black HDMI 1.4b HDMI Cord Male to Male Jacket: PVC Shield: Al-Mylar foil w/ Braid CL2 Fire Rated ARC, Deep Color, HDCP 1.4, CEC 2-Year Warranty Note: HDMI connector labelled "TV" connects to the display side

Hardware

Warranty	2 Years
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CL2 Rated
Chipset ID	Redmere - PRE1692

Performance

Maximum Digital Resolutions	4K x 2K @ 30 Hz
-----------------------------	-----------------

Connector(s)

Connector A	1 - HDMI (19 pin)
Connector B	1 - HDMI (19 pin)

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	28 AWG
Cable Length	32.8 ft [10 m]
Cable OD	0.3 in [7.5 mm]
Product Length	32.8 ft [10.0 m]
Product Width	0.0 in [0.0 cm]
Product Height	0.0 in [0.0 cm]
Weight of Product	1.3 lb [0.6 kg]

Packaging Information

Package Quantity	1
Package Length	13.0 in [33.0 cm]
Package Width	10.0 in [25.5 cm]
Package Height	1.9 in [4.8 cm]
Shipping (Package) Weight	1.3 lb [0.6 kg]

What's in the Box

Included in Package	1 - 10m Active High Speed HDMI Cable - HDMI - M/M
---------------------	---

**Product appearance and specifications are subject to change without notice.*