

10m (33 ft) Active CL2 In-wall High Speed HDMI Cable - Ultra HD 4k x 2k HDMI Cable - HDMI to HDMI - M/M

Product ID: HDMM10MA

The HDMM10MA 33 ft Active High Speed HDMI Cable features a built-in active signal booster for a connection distance of up to 33 feet (10m) between your HDMI-enabled devices, with no signal loss.

This durable yet lightweight cable features thinner HDMI wire construction that allows for a more flexible installation with minimal clutter. Plus, the cable features built-in amplifier circuitry which actively boosts the HDMI signal with no external power required.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

This 10 meter HDMI cable is backed by StarTech.com's 2-year Warranty.

This cable features unidirectional architecture which requires that the cable is installed in the correct direction. Please refer to the "source" and "display" labels on the HDMI connectors in order to ensure that the device and the HDMI source are connected properly.

Certifications, Reports and Compatibility



Applications

- Connecting high-definition A/V devices such as Blu-Ray Disc players, HDTVs, DVD Players, DVRs, game consoles, projectors etc., over long distances, with no signal loss

Features

- Built-in, active amplifier circuitry
- Gold-plated HDMI connectors
- High quality construction
- Supports Ultra HD Resolutions up to 4k x 2k
- Provides connection distances up to 33 feet away

Hardware	Warranty	2 Years
	Connector Plating	Gold
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Cable Shield Material	Aluminum-Mylar Foil with Braid
	Fire Rating	CL2 Rated
	Chipset ID	Redmere - PRE1692

Performance	Maximum Digital Resolutions	4K x 2K @ 30 Hz
Connector(s)	Connector A	HDMI (19 pin)
	Connector B	HDMI (19 pin)
Physical Characteristics	Color	Black
	Connector Style	Straight
	Wire Gauge	28 AWG
	Cable Length	32.8 ft [10 m]
	Cable OD	0.3 in [7.5 mm]
	Product Length	32.8 ft [10 m]
	Weight of Product	20.9 oz [593 g]
Packaging Information	Package Quantity	1
	Package Length	13.0 in [3.3 cm]
	Package Width	10.0 in [2.6 cm]
	Package Height	1.9 in [48 mm]
	Shipping (Package) Weight	21.5 oz [610 g]
What's in the Box	Included in Package	10m Active High Speed HDMI Cable - HDMI - M/M

**Product appearance and specifications are subject to change without notice.*

