

High Speed HDMI Cable M/M - 4K @ 30Hz - No Signal Booster Required - 15 m

**Product ID:** HDMM15M



This HDMI cable lets you connect your Ultra HD devices at distances of up to 15 meters, with no external power or active circuitry.

The cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high-definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4K x 2K.

The cable combines crystal-clear image resolutions with high-bandwidth video and multi-channel digital audio into a single cable.

The HDMM15M from StarTech.com is backed by a lifetime warranty for guaranteed reliability.

## Certifications, Reports and Compatibility

### Applications

- Connect high-definition A/V devices such as streaming media players, Blu-Ray Disc players, HDTVs, DVD Players, DVRs, game consoles, projectors etc.

### Features

- Supports Ultra HD Resolutions up to 3840x2160 (4K x 2K)
- Provides connection distances up to 15 meters away
- Guaranteed reliability with our lifetime warranty

---

**Hardware**

Warranty	Lifetime
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

---

**Performance**

Maximum Digital Resolutions	4K x 2K @ 30 Hz
-----------------------------	-----------------

---

**Connector(s)**

Connector A	HDMI (19 pin)
Connector B	HDMI (19 pin)

---

**Physical Characteristics**

Color	Black
Connector Style	Straight
Wire Gauge	24 AWG
Cable Length	49.2 ft [15 m]
Product Length	49.2 ft [15.0 m]
Product Width	0.8 in [20.0 mm]
Product Height	0.4 in [10.7 mm]
Weight of Product	3.6 lb [1.6 kg]

---

**Packaging Information**

Package Quantity	1
Package Length	17.5 in [44.5 cm]
Package Width	13.6 in [34.5 cm]
Package Height	2.6 in [65.0 mm]
Shipping (Package) Weight	3.8 lb [1.7 kg]



---

**What's in the  
Box**

Included in Package	15 m High Speed HDMI Cable - HDMI - M/M
---------------------	---

---

***\*Product appearance and specifications are subject to change without notice.***

