

High Speed HDMI Cable M/M - 4K @ 30Hz - No Signal Booster Required - 15 m

**Product ID:** HDMM15M



This HDMI cable lets you connect your Ultra HD devices at distances of up to 15 meters, with no external power or active circuitry.

The cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high-definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4K x 2K.

The cable combines crystal-clear image resolutions with high-bandwidth video and multi-channel digital audio into a single cable.

The HDMM15M from StarTech.com is backed by a lifetime warranty for guaranteed reliability.

## Certifications, Reports and Compatibility



## Applications

- Connect high-definition A/V devices such as streaming media players, Blu-Ray Disc players, HDTVs, DVD Players, DVRs, game consoles, projectors etc.

## Features

- Supports Ultra HD Resolutions up to 3840x2160 (4K x 2K)

- Provides connection distances up to 15 meters away
- Guaranteed reliability with our lifetime warranty

---

#### Hardware

|                       |                                |
|-----------------------|--------------------------------|
| Warranty              | Lifetime                       |
| Connector Plating     | Gold                           |
| Cable Jacket Material | PVC - Polyvinyl Chloride       |
| Cable Shield Material | Aluminum-Mylar Foil with Braid |

---

#### Performance

|                             |                 |
|-----------------------------|-----------------|
| Maximum Digital Resolutions | 4K x 2K @ 30 Hz |
|-----------------------------|-----------------|

---

#### Connector(s)

|             |                   |
|-------------|-------------------|
| Connector A | 1 - HDMI (19 pin) |
| Connector B | 1 - HDMI (19 pin) |

---

#### Environmental

|                       |                                  |
|-----------------------|----------------------------------|
| Operating Temperature | 0C to 50C (32F to 122F)          |
| Storage Temperature   | -20C to 70C (-4F to 158F)        |
| Humidity              | 0 to 95% (non-condensing) at 25C |

---

#### Physical Characteristics

|                 |                  |
|-----------------|------------------|
| Color           | Black            |
| Connector Style | Straight         |
| Wire Gauge      | 24 AWG           |
| Cable Length    | 49.2 ft [15 m]   |
| Cable OD        | 0.4 in [10 mm]   |
| Product Length  | 49.2 ft [15.0 m] |
| Product Width   | 0.8 in [2.0 cm]  |
| Product Height  | 0.4 in [1.1 cm]  |

|                   |                 |
|-------------------|-----------------|
| Weight of Product | 3.6 lb [1.6 kg] |
|-------------------|-----------------|

---

**Packaging Information**

|                           |                   |
|---------------------------|-------------------|
| Package Quantity          | 1                 |
| Package Length            | 11.7 in [29.7 cm] |
| Package Width             | 13.7 in [34.9 cm] |
| Package Height            | 2.6 in [6.6 cm]   |
| Shipping (Package) Weight | 3.6 lb [1.6 kg]   |

---

**What's in the Box**

|                     |   |
|---------------------|---|
| Included in Package | 1 - 15 m High Speed HDMI Cable - HDMI - M/M |
|---------------------|---|

---

***\*Product appearance and specifications are subject to change without notice.***