

1m HDMI Cable - 4K High Speed HDMI Cable with Ethernet - 4K 30Hz UHD HDMI Cord - 10.2 Gbps Bandwidth - HDMI 1.4 Video / Display Cable M/M 28AWG - HDCP 1.4 - Black

Produkt ID: HDMM1MHS



The HDMM1MHS 1-meter High Speed HDMI® Cable with Ethernet supports the advanced capabilities of the High-Definition Multimedia Interface, including Ethernet data inter-connectivity with compatible HDMI-enabled products, and is fully backward compatible with older HDMI-capable devices.

The cable features gold-plated HDMI (male) connectors which help to ensure a high quality digital connection capable of transmitting high-definition video and multi-channel audio between devices such as Blu-Ray Disc™ players, HDTVs, DVD Players, DVRs, stereo receivers and more.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

All StarTech.com High Speed HDMI Cables are expertly designed and constructed of top quality materials to deliver dependable high-definition performance, and are backed by Lifetime Warranty.

## Certifikat, rapporter och kompatibilitet

### Användning

- Quick-connect single HDMI® cable replaces multiple audio and video cables, reducing clutter and hassle
- Connecting high-definition A/V devices such as Blu-Ray Disc™ players, HDTVs, DVRs, etc.
- Connecting HDMI-equipped devices such as DVD players, game consoles, etc.

- Enables multiple devices to share an Internet connection (where applicable, device must support High Speed HDMI® with Ethernet)

## Funktioner

- **HIGH SPEED HDMI CABLE:** 1m (3.3ft) HDMI Cable with Ethernet supports 4K (3840x2160p, 24, 25, 30Hz | 4096x2160p, 24Hz), Full HD (1920x1080p, 120Hz), 10.2 Gbps bandwidth, wide aspect ratio, 8Ch Audio (5.1/7.1/DD+/Dolby TrueHD), 3D Video
- **DURABLE:** Ultra HD high speed fully molded 4K HDMI cable with durable PVC jacket for high strength and reliability; Flexible PVC strain relief prevents fraying or damage due to repetitive bending or rough usage; Ideal for Commercial environments
- **QUALITY CONSTRUCTION:** This HDMI to HDMI cable has a 28AWG wire with gold-plated connectors, and superior EMI shielding with Al-Mylar foil and copper braid (85% coverage) improve signal integrity and reliability, providing higher quality video and audio
- **APPLICATIONS:** Use in home offices/boardrooms/conference rooms/offices/classrooms, works with your laptop/professional workstation/soundbar for presentations via UHD/4K monitors, projector or large display; Samsung/Sony/Apple TV/Dell/Lenovo
- x
- **SPECS:** 1 m (3.3 ft) | Black | HDMI 1.4b | HDMI Cord Male to Male | 28 AWG | Gold-plated connectors | PVC Jacket | Shield: Al-Mylar foil w/ 85% Braid | ARC, Deep Color, HDCP 1.4, CEC | YCC601 Color | Supports HDMI 1.4 and earlier

---

### Hårdvara

Garantipolicy	Lifetime
Antal ledare	19
Kontaktplätering	Guld
Kabelmanteltyp	PVC - Polyvinyl Chloride

---

### Prestanda

Maximal digital upplösning	4K x 2K @ 30 Hz
----------------------------	-----------------

---

### Kontakt(er)

Connector A	HDMI (19-stifts)
Connector B	HDMI (19-stifts)

---

Utseende

Färg	Svart
Kontakttyp	Rak
Tråddimension	28 AWG
Kabellängd	39.4 in [100 cm]
Yttre kabeldiameter	0.3 in [7.3 mm]
Produktlängd	39.4 in [100.0 cm]
Produktbredd	0.8 in [20.0 mm]
Produkt höjd	0.5 in [12.0 mm]
Produktvikt	3.4 oz [95.0 g]

---

Förpackning

Förpackningsantal	1
Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	0.8 in [21.0 mm]
Fraktvikt (förpackning)	3.5 oz [100.0 g]

---

Vad det är i lådan

Ingår i paketet	1m High Speed HDMI® Cable with Ethernet - HDMI - M/M
-----------------	--

---

\* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

