

66ft (20m) Active HDMI Cable - 4K High Speed HDMI Cable with Ethernet - CL2 Rated for In-Wall Install - 4K 30Hz Video - HDMI 1.4 Cord - For HDMI Monitor, Projector, TV, Display

**Product ID:** HDMM20MA



This active HDMI cable offers a connection distance of up to 65 feet (20 meters) between your HDMI enabled devices. It meets CL2 rating safety requirements, so it's ideal for in-wall cable runs in your home and office installations.

The cable features built-in amplifier circuitry which actively boosts your HDMI signal, with no external power required. It's the perfect solution for longer transmissions without any signal loss.

The HDMI cable is CL2 rated for in-wall installations, which makes them perfect for A/V installations in residential or office settings. You can set up your home theatre, gaming or audio-video equipment with the cables hidden away safely inside the walls and place your devices as needed throughout your work or living space.

This high-quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high-definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

The HDMM20MA is backed by StarTech.com's 2-year Warranty for guaranteed reliability.

Note: This cable features unidirectional architecture which requires that the cable is installed in the correct direction. Please refer to the Source and Display labels on the HDMI connectors in order to ensure that the device and the HDMI source are connected properly.

## Certifications, Reports and Compatibility



## Applications

- Connect your high-definition A/V devices such as streaming media players (Roku, Apple TV), game consoles (Xbox One, PS4), Blu-ray Disc or DVD players over long distances, with no signal loss

## Features

- **HIGH SPEED HDMI CABLE:** 65.6 ft (20m) Active HDMI Cable with Ethernet supports 4K Ultra HD video (3840x2160p, 24, 30Hz 4096x2160p, 24Hz), Full HD (1080p 120Hz) HDMI 1.4b wide aspect ratio, 8Ch Audio (5.1/7.1/DD+/Dolby TrueHD), 3D Video
- **ACTIVE CIRCUITRY:** Active bus powered amplifier boosts video signals over longer distances to extend HDMI signal up to 65.6 ft (20m) (no external power supply needed), supports additional color spaces such as Adobe RGB and YCC601 Color
- **DURABLE CABLE:** Ideal for in-wall installations where CL2 rating is required; Flexible PVC jacket; Al-Mylar Foil with Braid shield & gold plated connectors with metal shell improve signal integrity & block external Electromagnetic Interference (EMI)
- **APPLICATIONS:** Use this long HDMI cable for home office, conference room, office or classroom; works w/ your laptop/professional workstation/soundbar for presentations via UHD/4K monitors, projectors/large HDTV displays; Samsung/Sony/Apple TV/Dell/Lenovo
- **SPECS:** 65.6 feet (20 meters) Black HDMI 1.4b HDMI Cord Male to Male Jacket: PVC Shield: Al-Mylar foil w/ Braid CL2 Fire Rated ARC, Deep Color, HDCP 1.4, CEC 2-Year Warranty Note: HDMI connector labelled "TV" connects to the display side

---

### Hardware

Warranty	2 Years
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CL2 Rated
Chipset ID	Redmere - RM1691

---

### Performance

Maximum Digital Resolutions	4K x 2K @ 30 Hz
-----------------------------	-----------------

---

### Connector(s)

Connector A	1 - HDMI (19 pin)
Connector B	1 - HDMI (19 pin)

---

**Physical Characteristics**

Color	Black
Connector Style	Straight
Wire Gauge	24 AWG
Cable Length	65.6 ft [20 m]
Cable OD	0.3 in [8.5 mm]
Product Length	65.6 ft [20 m]
Product Width	0.8 in [20 mm]
Product Height	0.4 in [0.9 cm]
Weight of Product	3.0 lb [1.4 kg]

---

**Packaging Information**

Package Quantity	1
Package Length	13.3 in [33.8 cm]
Package Width	12.8 in [32.6 cm]
Package Height	3.2 in [82 mm]
Shipping (Package) Weight	3.8 lb [1.7 kg]

---

**What's in the Box**

Included in Package	1 - 20m Active CL2 In-Wall High Speed HDMI Cable - HDMI - M/M
---------------------	---

---

***\*Product appearance and specifications are subject to change without notice.***