

## 2m High Speed HDMI Cable with Ethernet - Ultra HD 4k x 2k HDMI Cable - HDMI to HDMI M/M

Produkt ID: HDMM2MHS



The HDMM2MHS 2-meter High Speed HDMI® Cable with Ethernet supports the advanced capabilities of the High-Definition Multimedia Interface, including Ethernet data inter-connectivity with compatible HDMI-enabled products, and is fully backward compatible with older HDMI-capable devices.

The cable features gold-plated HDMI (male) connectors which help to ensure a high quality digital connection capable of transmitting high-definition video and multi-channel audio between devices such as Blu-Ray Disc™ players, HDTVs, DVD Players, DVRs, stereo receivers and more.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

All StarTech.com High Speed HDMI Cables are expertly designed and constructed of top quality materials to deliver dependable high-definition performance, and are backed by Lifetime Warranty.

### Certifikat, rapporter och kompatibilitet

#### Användning

- Quick-connect single HDMI® cable replaces multiple audio and video cables, reducing clutter and hassle
- Connecting high-definition A/V devices such as Blu-Ray Disc™ players, HDTVs, DVRs, etc.
- Connecting HDMI-equipped devices such as DVD players, game consoles, etc.

- Enables multiple devices to share an Internet connection (where applicable, device must support High Speed HDMI® with Ethernet)

## Funktioner

- 3D and Ethernet ready (for supported devices)
- Gold-plated HDMI® connectors
- High quality construction
- Supports Ultra HD Resolutions up to 4k x 2k

---

### Hårdvara

Garantipolicy	Lifetime
Antal ledare	19
Kontaktplätering	Guld
Kabelmanteltyp	PVC - Polyvinyl Chloride

---

### Prestanda

Maximal digital upplösning	4K x 2K @ 30 Hz
----------------------------	-----------------

---

### Kontakt(er)

Connector A	HDMI (19-stifts)
Connector B	HDMI (19-stifts)

---

### Miljö

Drifttemperatur	0°C to 35°C (32°F to 95°F)
Förvaringstemperatur	-10°C to 80°C (14°F to 176°F)
Luftfuktighet	5%-90% RH (icke-kondenserande)

---

### Utseende

Färg	Svart
Kontakttyp	Rak



Tråddimension	28 AWG
Kabellängd	6.6 ft [2 m]
Yttre kabelldiameter	0.3 in [7.3 mm]
Produktlängd	6.6 ft [2.0 m]
Produktbredd	0.8 in [20.2 mm]
Produkt höjd	0.4 in [10.3 mm]
Produktvikt	5.6 oz [158.0 g]

---

Förpackning

Förpackningsantal	1
Package Length	7.9 in [20.0 cm]
Package Width	8.7 in [22.0 cm]
Package Height	0.0 in [0.1 mm]
Fraktvikt (förpackning)	5.9 oz [166.0 g]

---

Vad det är i lådan

Ingår i paketet	2m High Speed HDMI® Cable with Ethernet - HDMI - M/M
-----------------	--

---

\* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

