

Premium High Speed HDMI Cable with Ethernet - 4K 60Hz - 2 m (6 ft.)

Product ID: HDMM2MP



This 2-meter High Speed HDMI cable has been tested in accordance with the Premium HDMI Cable Certification Program. This ensures it's able to deliver the newest technical features that the latest HDMI specifications have to offer, including enhanced resolutions and protection against EMI interference.

Each of our certified Premium High Speed HDMI Cables is labeled with unique anti-counterfeiting authentication, so you can be confident that you have received a genuine certified cable.

The cable supports resolutions of up to 4K@60Hz(3840x2160p) and bandwidths of up to 18Gbps. It also supports HDR (High Dynamic Range) for higher contrast ratio and vivid colors.

With higher resolutions, increased speeds, and sharper images, you can expect an enhanced video experience. The cable is guaranteed to provide the very best HDMI capabilities available today. It's the perfect cable for creating dependable home theater connections or providing lifelike digital signage.

Plus, the cable also supports up to 32 uncompressed digital audio channels to provide crystal-clear sound. The cable is also backward compatible with previous HDMI specifications and will work with all of your existing HDMI devices.

The cable has undergone rigorous compliance testing and is certified by an HDMI Authorized Test Center. This gives you the assurance that the cable will deliver the high-bandwidth enabled features you need. An EMI test is also performed to ensure the cable minimizes interference with wireless signals.

The cable delivers dual video streams so that you can view two videos simultaneously on the same display. Your display must support Multi-View in order to take advantage of dual video streams.

The HDMM2MP is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility





Applications

- Connect 4K/Ultra HD displays and devices

Features

- Premium HDMI certification
- Supports resolutions up to 4K@60 Hz
- Supports up to 18Gbps bandwidth
- Backward compatible with earlier versions of HDMI
- Up to 32 audio channels with 1536Hz sampling rate
- Supports 21:9 cinema aspect ratio
- Delivers dual video streams to a single display
- Delivers multi-stream audio to multiple users (up to 4)
- Supports BT.2020 colorimetry
- Supports Consumer Electronics Control (CEC) functions
- Supports HDR (High Dynamic Range) for expanded contrast ratio and color accuracy
- Supports all HDMI 2.0 specifications
- Supports 3D video

Hardware	Warranty	Lifetime
	Connector Plating	Gold
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Cable Shield Material	Aluminum-Mylar Foil with Braid
Performance	Audio Specifications	Up to 32 audio channels with 1536Hz sampling rate
Connector(s)	Connector A	HDMI (19 pin)
	Connector B	HDMI (19 pin)
Physical Characteristics	Color	Black
	Connector Style	Straight
	Wire Gauge	30 AWG
	Cable Length	6.6 ft [2 m]
	Product Length	6.6 ft [2 m]
	Weight of Product	4.4 oz [125 g]
Packaging	Package Length	10.3 in [2.6 cm]

Information

Package Width	7.0 in [1.8 cm]
Package Height	1.4 in [36 mm]
Shipping (Package) Weight	7.2 oz [204 g]

What's in the Box	Included in Package	2m Premium High Speed HDMI Cable
--------------------------	---------------------	----------------------------------

****Product appearance and specifications are subject to change without notice.***

