

30m (100 ft) Active Fiber Optic AOC High Speed HDMI Cable M/M - Ultra HD 4k x 2k HDMI Cable

**Product ID:** HDMM30MAO



The HDMM30MAO Active Optical High Speed HDMI Cable features both copper and fiber conductors, providing a lighter, more flexible cable construction, which makes it ideal for installation in narrow spaces and over longer distances - a perfect solution for conference rooms, classrooms, digital signage displays, and more.

The HDMI AOC features a built-in booster circuit that is self-powered through the HDMI ports, allowing you to connect your HDMI-enabled devices at a distance of up to 30 meters with no signal loss.

Comprised of a fiber and copper wire mix, this active cable is less susceptible to EMI interference, for a clear and reliable Audio/Video signal even in environments such as data centers, hospitals, etc.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

This 30-meter HDMI cable is backed by StarTech.com's 2-year Warranty.

Please Note: This cable features unidirectional architecture, which requires that the cable is installed in the correct direction. Please refer to the "source" and "display" labels on the HDMI connectors, in order to ensure that the device and the HDMI source are connected properly.

## Certifications, Reports and Compatibility



## Applications

- Connecting high-definition A/V devices such as Blu-Ray Disc players, HDTVs, DVD Players, DVRs, game consoles, projectors etc., over longer distance with no signal loss or EMI interference

## Features

- Powered by HDMI ports
- Fiber optic and copper wire
- EMI/RFI immunity
- Supports Ultra HD Resolutions up to 4k x 2k

---

### Hardware

|                       |                          |
|-----------------------|--------------------------|
| Warranty              | 2 Years                  |
| Connector Plating     | Gold                     |
| Cable Jacket Material | PVC - Polyvinyl Chloride |

---

### Performance

|                             |                 |
|-----------------------------|-----------------|
| Maximum Digital Resolutions | 4K x 2K @ 30 Hz |
|-----------------------------|-----------------|

---

### Connector(s)

|             |                   |
|-------------|-------------------|
| Connector A | 1 - HDMI (19 pin) |
| Connector B | 1 - HDMI (19 pin) |

---

### Environmental

|                       |                           |
|-----------------------|---------------------------|
| Operating Temperature | 0C to 50C (32F to 122F)   |
| Storage Temperature   | -20C to 70C (-4F to 158F) |

---

### Physical Characteristics

|                 |                  |
|-----------------|------------------|
| Color           | Black            |
| Connector Style | Straight         |
| Cable Length    | 98.4 ft [30 m]   |
| Product Length  | 98.4 ft [30.0 m] |
| Product Width   | 0.8 in [2.0 cm]  |
| Product Height  | 0.4 in [1.0 cm]  |

|                   |                 |
|-------------------|-----------------|
| Weight of Product | 2.4 lb [1.1 kg] |
|-------------------|-----------------|

---

**Packaging Information**

|                           |                   |
|---------------------------|-------------------|
| Package Quantity          | 1                 |
| Package Length            | 10.3 in [26.2 cm] |
| Package Width             | 10.3 in [26.1 cm] |
| Package Height            | 3.2 in [81.0 mm]  |
| Shipping (Package) Weight | 3.0 lb [1.4 kg]   |

---

**What's in the Box**

|                     |  |
|---------------------|--|
| Included in Package | 1 - 30m Active Optical High Speed HDMI Cable |
|---------------------|--|

---

***\*Product appearance and specifications are subject to change without notice.***