

3m (10ft) HDMI Cable - 4K High Speed HDMI Cable with Ethernet - UHD 4K 30Hz Video - HDMI 1.4 Cable - Ultra HD HDMI Monitors, Projectors, TVs & Displays - Black HDMI Cord - M/M

**Product ID:** HDMM3M



The HDMM3M High Speed HDMI cable (3m/9.8ft) features 2 gold-plated HDMI (male) connectors and durable high quality construction to provide a dependable HDMI to HDMI connection between devices such as Blu-Ray Disc players, HDTVs, DVD Players, stereo receivers, projectors and more.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

The HDMM3M 3-meter/9.8ft HDMI cable is backed by StarTech.com's Lifetime Warranty.

About StarTech.com HDMI to HDMI Cables:

StarTech.com High Speed HDMI digital video and audio cables are expertly designed and constructed of only top quality materials to ensure high quality, high definition performance. The HDMI standard combines high bandwidth video and multi-channel digital audio into a single cable, and provides crystal clear image resolution.

Please Note: This is a replacement product for StarTech.com's 10 ft High Speed HDMI Cable - HDMI- M/M (HDMIMM10).

## Certifications, Reports and Compatibility



## Applications

- Connecting high-definition A/V devices such as Blu-Ray Disc players, HDTVs, DVD Players, DVRs, game consoles, projectors etc.
- A convenient, single-cable solution for connecting high-definition set-top boxes, A/V receivers

## Features

- **HIGH SPEED HDMI CABLE:** 9.8 ft (3m) HDMI 1.4b Cable with Ethernet supports 4K video (3840x2160p, 24, 25, 30Hz 4096x2160p, 24Hz), Full HD (1920x1080p, 120Hz), 10.2 Gbps bandwidth, wide aspect ratio, 8Ch Audio (5.1/7.1/DD+/Dolby TrueHD), 3D Video
- **DURABLE:** 9.8ft Ultra HD 4K high speed HDMI cable (fully molded) with durable PVC jacket for high strength and reliability; Flexible PVC strain relief prevents fraying/damage due to repetitive bending or rough usage
- **QUALITY CONSTRUCTION:** 30AWG wire with gold-plated connectors, and superior EMI shielding with Al-Mylar foil & copper braid improve signal integrity and reliability, providing higher quality video & audio with this HDMI 1.4 cable
- **APPLICATIONS:** Use this 4K HDMI cable in home offices, conference rooms, offices or classrooms; works with your laptop, professional workstation & soundbar for presentations via UHD/4K monitor, projector or large display; Samsung/Sony/Apple TV/Dell/Lenovo
- **SPECS:** 9.8 foot (3 meters) Black HDMI 1.4b HDMI Cord Male to Male 30 AWG Gold-plated connectors PVC Jacket Shield: Al-Mylar foil w/ 65% Braid ARC, Deep Color, HDCP 1.4, CEC YCC601 Color Supports HDMI 1.4 and earlier Lifetime Warranty

---

### Hardware

Warranty	Lifetime
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

---

### Performance

Maximum Digital Resolutions	4K x 2K @ 30 Hz
-----------------------------	-----------------

---

### Connector(s)

Connector A	1 - HDMI (19 pin)
Connector B	1 - HDMI (19 pin)

---

### Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-20C to 70C (-4F to 158F)

Humidity 60% at 25C

---

**Physical Characteristics**

Color	Black
Connector Style	Straight
Wire Gauge	28 AWG
Cable Length	9.8 ft [3 m]
Product Length	9.8 ft [3.0 m]
Product Width	0.8 in [20.8 mm]
Product Height	0.4 in [1.1 cm]
Weight of Product	7.1 oz [202.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	15.6 in [39.5 cm]
Package Width	5.4 in [13.8 cm]
Package Height	0.9 in [24.0 mm]
Shipping (Package) Weight	7.3 oz [207.0 g]

---

**What's in the Box**

Included in Package	1 - 3m High Speed HDMI Cable - HDMI - M/M
---------------------	---

---

*\*Product appearance and specifications are subject to change without notice.*