

9.8ft (3m) HDMI 2.0 Cable, 4K 60Hz Premium Certified High Speed HDMI Cable w/ Ethernet, Ultra HD HDMI Cable, Long HDMI Cable/Cord for TV/Monitor/Laptop/PC, HDMI to HDMI Video

Product ID: HDMM3MLP



This 3-meter HDMI cable has been tested in accordance with the Premium HDMI Cable Certification Program. This ensures it's able to deliver the newest technical features that the latest HDMI specifications have to offer, including enhanced resolutions and protection against EMI interference.

The cable features high-retention HDMI connectors that fasten firmly inside each port. This helps to prevent accidental disconnections and signal loss.

Each cable is labeled with the Premium HDMI Cable authentication, so you can be confident that you are purchasing a high-quality premium cable with guaranteed performance.

The cable supports resolutions of up to 4K@60Hz (3840x2160p) and bandwidths of up to 18Gbps. It also supports HDR (High Dynamic Range) for higher contrast ratio and vivid colors.

With higher resolutions, increased speeds, and sharper images, you can expect an enhanced video experience. The cable is guaranteed to provide the very best HDMI capabilities available today. It's the perfect cable for creating the ultimate home theater or for providing lifelike digital signage.

Plus, the cable also supports up to 32 uncompressed digital audio channels to provide crystal-clear sound. The cable is also backward compatible with previous HDMI specifications and will work with all of your existing HDMI devices.

The gripping HDMI connectors are ideal for high traffic applications or in environments where vibrations could cause accidental disconnects and picture loss. It works great with wall-mounted equipment and in situations where equipment is frequently moved.

Plug the connectors inside the HDMI ports and the connectors will automatically latch to the inside of the port, there are no special screws or accessories required. The grips will create contact pressure inside the port and ensure that the connectors don't loosen over time.

The cable has undergone rigorous compliance testing and is certified by an HDMI Authorized Test Center to ensure it supports the high-bandwidth enabled features it promises. An EMI test is also performed to ensure the cable

minimizes interference with wireless signals.

The HDMM3MLP is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

Features

- **HIGH PERFORMANCE CABLE:** 9.8 ft (3 m) Premium Certified HDMI 2.0 with Ethernet, 4K 60Hz (3840x2160p), 18Gbps bandwidth, HDR10 for high contrast ratio, Ultra wide aspect ratio, 32 Ch. multi-stream audio w/1536Hz sampling (5.1/7.1/DD+/Dolby TrueHD/Atmos) -
- **HDMI 2.0 CABLE WITH GRIPPING CONNECTORS:** This Premium Certified High Speed HDMI cable with Ethernet features gold plated gripping male connectors that fasten firmly inside a standard HDMI port to prevent disconnection due to tension or vibration -
- **CERTIFIED HIGH QUALITY CABLE:** Long lasting & heavy duty PVC jacket absorbs stress of frequent bends protecting the core of the UHD HDMI cord; Premium High Speed certification ensures that each cable meets the HDMI 2.0 standards -
- **APPLICATIONS:** For office/boardrooms/classrooms; Connect your laptop/computer/HDMI source to your TV/display/monitor/projector; Ideal in environments that demand frequent movement/vibration; Samsung/Dell/HP/Acer/LG; Supports HDMI 1.4 and earlier -
- **SPECS:** 9.8 feet (3 meters) Black Premium High Speed Cable with Ethernet HDMI Gripping Male to Gripping Male (M/M) 7.3 mm (0.29") OD, 34AWG Jacket: PVC EMI Shield: Al-Mylar Foil, Braid

Hardware

Warranty	Lifetime
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Maximum Digital Resolutions	3840 x 2160 (Ultra HD 4K) @ 60hz
-----------------------------	----------------------------------

Connector(s)

Connector A	HDMI (19 pin)
-------------	---------------

Connector B	HDMI (19 pin)
-------------	---------------

Environmental

Operating Temperature	0C to 60C (32F to 140F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	5%RH ~ 95%RH

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	28 AWG
Cable Length	9.8 ft [3 m]
Product Length	9.8 ft [3.0 m]
Product Width	0.8 in [20.0 mm]
Product Height	0.4 in [10.5 mm]
Weight of Product	8.2 oz [232.0 g]

Packaging Information

Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	0.8 in [21.0 mm]
Shipping (Package) Weight	8.6 oz [244.0 g]

What's in the Box

Included in Package	HDMI Cable
---------------------	------------

****Product appearance and specifications are subject to change without notice.***

