

High Speed HDMI Cable M/M - 4K @ 30Hz - No Signal Booster Required - 45 ft.

Product ID: HDMM45



This HDMI cable lets you connect your Ultra HD devices at distances of up to 45 feet, with no external power or active circuitry.

The cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high-definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4K x 2K.

The cable combines crystal-clear image resolutions with high-bandwidth video and multi-channel digital audio into a single cable.

The HDMM45 from StarTech.com is backed by a lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Connect high-definition A/V devices such as streaming media players, Blu-Ray Disc players, HDTVs, DVD Players, DVRs, game consoles, projectors etc.

Features

- Supports Ultra HD Resolutions up to 3840x2160 (4K x 2K)

- Provides connection distances up to 45 feet away
- Guaranteed reliability with our lifetime warranty

Hardware

Warranty	Lifetime
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Maximum Digital Resolutions	4K x 2K @ 30 Hz
-----------------------------	-----------------

Connector(s)

Connector A	1 - HDMI (19 pin)
Connector B	1 - HDMI (19 pin)

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	24 AWG
Cable Length	45.0 ft [13.7 m]
Cable OD	0.4 in [10 mm]
Product Length	45.0 ft [13.7 m]
Product Width	0.8 in [2.0 cm]
Product Height	0.4 in [1.1 cm]
Weight of Product	3.4 lb [1.6 kg]

Packaging Information

Package Quantity	1
Package Length	18.1 in [46.0 cm]



Package Width	13.8 in [35.0 cm]
Package Height	3.8 in [9.7 cm]
Shipping (Package) Weight	3.5 lb [1.6 kg]

What's in the Box

Included in Package	1 - 45ft High Speed HDMI Cable - HDMI - M/M
---------------------	---

****Product appearance and specifications are subject to change without notice.***

