

50ft (15m) High Speed HDMI Cable M/M - 4K @ 30Hz - No Signal Booster Required

ID prodotto: HDMM50



This High Speed HDMI™ Cable is designed to deliver superior video and audio performance while ensuring reliable connectivity with a variety of HDMI devices, including HDTVs, stereo receivers, projectors, gaming consoles, and more.

High Speed HDMI™

This HDMI 1.4b cable supports Ultra HD 4K resolutions (3840x2160p at 30Hz, or 4096x2160p at 24Hz), Full HD (1920x1080p at up to 120Hz), and a bandwidth of 10.2 Gbps for seamless video and audio transmission. It also supports wide aspect ratios, making it perfect for both home entertainment systems and professional presentations. With support for 3D video and multi-channel audio, you can enjoy a fully immersive viewing and listening experience.

Constructed with 24 AWG copper wire, gold-plated connectors, and superior EMI shielding using Al-Mylar foil and a copper braid, this cable minimizes signal loss and interference. This ensures clear, high-quality audio and video transmission with exceptional reliability.

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

Certificazioni, report e compatibilità



Applicazioni

- Connect high-definition A/V devices such as streaming media players, Blu-Ray Disc™ players, HDTVs, DVD Players, DVRs, game consoles, projectors etc.

Caratteristiche

- Supports Ultra HD Resolutions up to 3840x2160 (4K x 2K)
- Consente distanze di collegamento fino a 15 m
- Affidabilità assicurata con la nostra garanzia a vita

Hardware

Norme di garanzia	Lifetime
Placcatura connettori	Oro
Tipo guaina cavo	PVC - Polyvinyl Chloride
Tipo schermatura cavo	Foglio di alluminio mylar con treccia

Prestazioni

Risoluzioni digitali massime	4K x 2K @ 30 Hz
------------------------------	-----------------

Connettore/i

Connettore A	1 - HDMI (19 pin)
Connettore B	1 - HDMI (19 pin)

Caratteristiche fisiche

Colore	Nero
Stile connettori	Dritto
Diametro filo	24 AWG
Lunghezza del cavo	50.0 ft [15.2 m]
OD cavo	0.4 in [10 mm]
Lunghezza prodotto	50.0 ft [15.2 m]
Larghezza prodotto	0.8 in [2.0 cm]

Altezza prodotto	0.4 in [1.1 cm]
Peso prodotto	3.6 lb [1.6 kg]

Informazioni confezione

Quantità confezione	1
Lunghezza Confezione	12.8 in [32.5 cm]
Larghezza del Pacco	13.7 in [34.7 cm]
Altezza del Pacco	2.6 in [6.5 cm]
Peso spedizione (confezione)	3.7 lb [1.7 kg]

Contenuto della confezione

Incluso nella confezione	1 - Cavo HDMI® ad alta velocità da 15,2 m - HDMI - M/M
--------------------------	--

Informazioni sulla garanzia

Warranty	A vita
----------	--------

* L'aspetto e le specifiche dell'articolo sono soggetti a modifiche senza preavviso.