

15ft (4.5m) Premium Certified High Speed HDMI Cable, 4K 60Hz/1440p 144Hz, HDMI 2.0 Cable with HDR10/ARC, 18Gbps, 4K HDMI Cord for Monitor/TV/Display, High-Flex TPE Jacket

**Product ID:** HDMMV15F



Drive sharp 4K UHD video, fast refresh rates, and high-resolution visuals on UHD displays, workstations, video walls, and AV installations. This Premium High Speed HDMI 2.0 cable supports 4K at 60Hz, 1440p at 144Hz, 1080p at up to 240Hz, and up to 18Gbps bandwidth for consistent, reliable signal quality.

Deliver deep contrast and accurate color with support for HDR10 and Dolby Vision. Enable immersive 32-channel audio using ARC, Dolby Atmos, DTS:X, and 7.1 Dolby TrueHD. Maintain secure content delivery with HDCP 2.2 across HDMI 2.0 and legacy devices.

The 4K HDMI Cable is certified by an HDMI Authorized Test Center and undergoes rigorous compliance testing to verify support for all HDMI 2.0 high-bandwidth features. It is EMI-tested to ensure minimal interference with nearby wireless signals. This cable works with all 4K ready devices and is backward compatible with previous HDMI specifications.

Route this HDMI cord easily around corners, behind displays, and through tight spaces with a high-flex, halogen-free TPE jacket engineered for tight bends in dense installations. The cable's flexibility supports clean routing in enterprise AV racks, workstations, and wall-mounted display setups without compromising durability.

Aluminum-Mylar foil with braided shielding minimizes EMI in shared environments, while reinforced connector strain reliefs protect against repeated bending. Gold-plated connectors preserve signal integrity, resist corrosion, and are rated for 10,000+ insertions for long-term, reliable use.

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

## Certifications, Reports and Compatibility



## Applications

- Deliver full HDMI 2.0 performance with backward compatibility
- Connect a high performance workstation to a 4K 60Hz UHD display

## Features

- **Deliver High-Bandwidth 4K Video**: 15ft (4.5m) HDMI 2.0 Cable delivers vivid, sharp 4K 60Hz UHD/1440p 144Hz video with HDR10, Dolby Vision, and HDCP 2.2; Enable immersive sound quality with 32-channel audio, 7.1 TrueHD, ARC, Dolby Atmos, and DTS:X support
- **Certified for Reliable Performance**: Use this Certified Premium High Speed HDMI cable for guaranteed HDMI 2.0 and backward compatibility across multiple resolutions and refresh rates; Operates seamlessly between current and legacy HDMI devices
- **Identify Specs Instantly**: HDMI spec markings on each Quick ID connector remove guesswork and confirm feature support at-a-glance; The eco-friendly TPE jacket is flexible and durable, designed to withstand tight bends and is fully RoHS-compliant
- **For High-Resolution Workflows**: Ideal for workstations and 4K UHD pro A/V setups; Achieve clear, sharp picture quality with 18Gbps bandwidth; Works with USB-C to HDMI adapters for DP Alt Mode devices and Apple M-series Pro/Max MacBooks
- **The IT Pro's Choice**: Our digital display cables are rigorously lab-tested for signal integrity, durability, and compatibility across HDMI, DisplayPort, USB-C, and legacy interfaces; Backed by free lifetime 24/5 multi-lingual technical assistance

---

### Hardware

Warranty	Lifetime
Active or Passive Adapter	Passive
Connector Plating	Gold
Cable Jacket Material	TPE - Thermoplastic Elastomers
Cable Shield Material	Aluminum-Mylar Foil with Braid

---

### Performance

Maximum Data Transfer Rate	18Gbps
----------------------------	--------

Maximum Digital Resolutions	5K 30Hz
	4K 60Hz
	1440p 144Hz
	1080p 240Hz

---

**Connector(s)**

Connector A	1 - HDMI
Connector B	1 - HDMI

---

**Environmental**

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 70C (-4F to 158F)
Humidity	10%RH ~ 90%RH

---

**Physical Characteristics**

Color	Black & Silver
Connector Style	Straight
Wire Gauge	28 AWG
Material	ABS
	Polycarbonate
Cable Length	15.0 ft [4.6 m]
Cable OD	0.3 in [6.5 mm]
Product Length	180.6 in [4588 mm]
Product Width	0.8 in [20.5 mm]
Product Height	0.4 in [11 mm]
Weight of Product	8.5 oz [242 g]

---

**Packaging Information**

Package Length	7.3 in [18.5 cm]
----------------	------------------

Package Width	7.7 in [19.5 cm]
Package Height	2.2 in [5.5 cm]
Shipping (Package) Weight	10.6 oz [300.0 g]

---

**What's in the Box**

Included in Package	1 - Premium High Speed HDMI Cable
---------------------	-----------------------------------

---

***\*Product appearance and specifications are subject to change without notice.***