

25ft (7.5m) Plenum Rated HDMI Cable, 4K High Speed Long HDMI Cord w/ Ethernet, 4K30Hz UHD, 10.2 Gbps, HDCP 1.4, In Wall Plenum HDMI 1.4 Display Cable, HDMI Computer to TV Cable

Produkt-ID: HDPMM25



This plenum-rated High Speed HDMI® cable can be installed in air plenums, ducts, walls, conduits, ceilings, or anywhere else a CMP/FT6 fire rating is required.

The cable features 2 gold-plated HDMI (male) connectors and durable construction to provide you with a dependable HDMI to HDMI connection between your A/V devices.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

About StarTech.com HDMI to HDMI Cables:

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

Zertifikate Berichte und Kompatibilität



Anwendungen

- HDMI installations where cable needs to be run through air ducts and plenums, where CMP fire

rating is required (educational or commercial installations, etc.)

- Connecting high-definition A/V devices such as Blu-Ray Disc™ players, HDTVs, DVD Players, DVRs, game consoles, projectors etc.

Merkmale

- **HIGH SPEED HDMI CABLE:** 25 ft (7.6 m) HDMI 1.4b Cable with Ethernet supports 4K (3840x2160p, 24, 25, 30Hz | 4096x2160p, 24Hz), Full HD (1920x1080p, 120Hz), 10.2 Gbps bandwidth, wide aspect ratio, 8Ch Audio (5.1/7.1/DD+/Dolby TrueHD), 3D Video
- **DURABLE PLENUM RATED CABLE:** Ultra HD fully molded HDMI cable with durable PVC jacket and strain relief for high strength and reliability; CMP fire rated cable for plenum installs: ducts, walls, conduits, ceilings; Ideal for Commercial environments
- **QUALITY CONSTRUCTION:** 24AWG wire with gold-plated connectors, and superior EMI shielding with Al-Mylar foil and braid improve signal integrity and reliability, providing higher quality video and audio; Supports HDMI 1.4 and earlier versions
- **APPLICATIONS:** Use in home offices/boardrooms/conference rooms/offices/classrooms, works with your laptop/professional workstation/soundbar for presentations via UHD/4K monitors, projector or large display; Samsung/Sony/Apple TV/Dell/Lenovo
- **SPECS:** 25 ft (7.6 m) | Black | HDMI 1.4b | HDMI Cord Male to Male | 24 AWG | Gold-plated connectors | PVC Jacket | Shield: Al-Mylar foil with Braid | ARC, Deep Color, HDCP 1.4, CEC | YCC601 Color | CMP Fire Rated

Hardware

Garantiebestimmungen	Lifetime
Steckverbinderplatten	Gold
Typ der Kabelummantelung	PVC - Polyvinyl Chloride
Typ der Kabelabschirmung	Aluminium-Mylar-Folie mit Geflecht
Feuerwiderstandssklasse	Ausgelegt gemäß CMP (Plenum)

Leistung

Max. Digitalauflösungen	4K x 2K @ 30 Hz
-------------------------	-----------------

Steckverbinder

Steckverbinder A	1 - HDMI (19-polig)
Steckverbinder B	1 - HDMI (19-polig)

Physische Eigenschaften

Farbe	Schwarz
Steckverbinderart	Gerade
Drahtstärke	24 AWG
Kabellänge	25.0 ft [7.6 m]
Produktlänge	25.0 ft [7.6 m]
Produktbreite	0.8 in [2.1 cm]
Produkthöhe	0.4 in [1.1 cm]
Produktgewicht	2.4 lb [1.1 kg]

Verpackungsinformationen

Paketmenge	1
Paketlänge	11.9 in [30.1 cm]
Paketbreite	13.7 in [34.8 cm]
Pakethöhe	2.3 in [5.8 cm]
Versandgewicht (Verpackung)	2.4 lb [1.1 kg]

Verpackungsinhalt

Im Paket enthalten	1 - 25 ft Plenum-Rated High Speed HDMI® Cable
--------------------	---

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.