

35ft (10.6m) Plenum Rated HDMI Cable, 4K High Speed Long HDMI Cord w/ Ethernet, 4K30Hz UHD, 10.2 Gbps, HDCP 1.4, In Wall Plenum HDMI 1.4 Display Cable, HDMI Computer to TV Cable

Produkt-ID: HDPMM35



The plenum-rated High Speed HDMI® cable can be installed in air plenums, ducts, walls, conduits, ceilings, or anywhere else a CMP/FT6 fire rating is required.

This cable features 2 gold-plated HDMI (male) connectors and durable construction to provide you with a dependable HDMI to HDMI connection between your A/V devices.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

About StarTech.com HDMI to HDMI Cables:

StarTech.com High Speed HDMI digital video and audio cables are expertly designed and constructed of only top quality materials to ensure high-quality, high-definition performance. The HDMI standard combines high bandwidth video and multi-channel digital audio into a single cable, and provides crystal clear image resolution.

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

Zertifikate Berichte und Kompatibilität



Anwendungen

- HDMI installations where cable needs to be run through air ducts and plenums, where CMP fire rating is required (educational or commercial installations, etc.)
- Anschließen von High Definition A/V-Geräten wie Blu-Ray Disc™-Player, HDTVs, DVD-Player, DVRs, Spielekonsolen, Projektoren usw.

Merkmale

- HIGH SPEED HDMI CABLE: 35 ft (10.7 m) HDMI 1.4b Cable with Ethernet supports 4K (3840x2160p, 24, 25, 30Hz | 4096x2160p, 24Hz), Full HD (1920x1080p, 120Hz), 10.2 Gbps bandwidth, wide aspect ratio, 8Ch Audio (5.1/7.1/DD+/Dolby TrueHD), 3D Video
- Goldbeschichtete -HDMI-Anschlüsse
- QUALITY CONSTRUCTION: 24AWG wire with gold-plated connectors, and superior EMI shielding with Al-Mylar foil and braid improve signal integrity and reliability, providing higher quality video and audio; Supports HDMI 1.4 and earlier versions
- APPLICATIONS: Use in home offices/boardrooms/conference rooms/offices/classrooms, works with your laptop/professional workstation/soundbar for presentations via UHD/4K monitors, projector or large display; Samsung/Sony/Apple TV/Dell/Lenovo
- SPECS: 35 ft (10.7 m) | Black | HDMI 1.4b | HDMI Cord Male to Male | 24 AWG | Gold-plated connectors | PVC Jacket | Shield: Al-Mylar foil with Braid | ARC, Deep Color, HDCP 1.4, CEC | YCC601 Color | CMP Fire Rated

Hardware

Garantiebestimmungen	Lifetime
Steckverbinderplatten	Gold
Typ der Kabelummantelung	PVC - Polyvinyl Chloride
Typ der Kabelabschirmung	Aluminium-Mylar-Folie mit Geflecht
Feuerwiderstandssklasse	Ausgelegt gemäß CMP (Plenum) e

Leistung	Max. Digitalauflösungen	4K x 2K @ 30 Hz
Steckverbinder	Steckverbinder A	1 - HDMI (19-polig)
	Steckverbinder B	1 - HDMI (19-polig)
Physische Eigenschaften	Farbe	Schwarz
	Steckverbinderart	Gerade
	Drahtstärke	24 AWG
	Kabellänge	35.0 ft [10.7 m]
	Produktlänge	35.0 ft [10.7 m]
	Produktgewicht	3.2 lb [1.4 kg]
Verpackungsinformationen	Paketmenge	1
	Paketlänge	13.1 in [33.4 cm]
	Paketbreite	13.7 in [34.7 cm]
	Pakethöhe	1.9 in [4.7 cm]
	Versandgewicht (Verpackung)	3.2 lb [1.5 kg]
Verpackungsinhalt	Im Paket enthalten	1 - 35 ft Plenum-Rated High Speed HDMI® Cable
Garantieinformationen	Warranty	Lifetime

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.