

4-pack 15ft (4.6m) Hook and Loop Roll, 0.5in Wide, Black, Cut-to-Size Reusable Cable Ties, Fastener Tape, Adjustable Fabric Wraps, Bulk Roll

Product ID: HKLP15054PK



This 4-pack of 15 ft (4.6 m) hook-and-loop cable tie rolls provides a total of 60 ft (21 m), making it easy to keep your cables neat and tidy by binding them together or to a structure. The self-gripping fabric can be cut to any length and is 0.5 in (12.7 mm) wide, offering a slim, wrap-around solution for virtually any cable in any environment.

This roll of cable tie offers a quick and easy solution for bundling cables together and securing your cables for better routing. Properly routed cables help protect your equipment, by reducing cable tension and preventing excessive heat caused by unorganized cables restricting airflow.

It uses a hook-and-loop fastening method to ensure a sturdy grip that's easy to apply. With the hook mechanism on one side of the tape and a loop mechanism on the other, you can easily wrap it around your cable bundle, and fasten the cable tie by draping it over itself.

Whether your bundle consists of two small-gauge cables or many large-gauge cables, you can rest assured this roll of cable tie will handle it perfectly. You can cut the hook-and-loop fabric to size using household scissors, meaning you can choose the perfect length for your specific application.

The versatility of the cable tie makes the roll the ideal tool for you to keep on hand in your office, server room or industrial environment.

While the most common use for this hook-and-loop fabric is binding and routing cables, you can also use it for other materials in your IT environment such as tools or raceways. The ties are easy to remove, reusable and adjustable, avoiding the hassle and waste of traditional zip ties.

Certifications, Reports and Compatibility

Applications

- Keep your office or server room neat and tidy, by binding your equipment cables together
- Prevent damage to your rack-mount equipment by routing cables to improve airflow and reduce port tension

Features

- **Custom-Length Cable Ties:** This 4-pack of 15 ft, 0.5 in wide reusable black hook and loop tape (total 60ft / 21m) allows you to cut and adjust cable ties to the length you need without the waste of traditional single-use zip ties
- **Reduce Cable Strain:** Industrial-strength hook and loop roll helps route cables neatly while relieving connector strain that can lead to port or device damage
- **Install Quickly with Adjustable Grip:** Self-gripping hook and loop fastener straps offer a quick and easy solution for bundling and securing cables, ideal for on-the-fly adjustments and streamlined installs
- **Protect Equipment:** Professional cable management keeps cables tidy and airflow unobstructed, supporting clean workspaces and thermal performance in racks and enclosures
- **The IT Pro's Choice:** Our industrial-grade cable tying solutions deliver strength, reusability, and easy installation across diverse environments, and are backed by free lifetime 24/5 multilingual technical support

Environmental

Warranty	2 Years
Operating Temperature	14F to 176F (-10C - 80C)
Storage Temperature	14F to 176F (-10C - 80C)

Physical Characteristics

Color	Black
Product Length	0.0 ft [0.0 m]
Product Width	0.5 in [12.7 mm]
Weight of Product	6.5 oz [185 g]

Packaging Information

Package Quantity	4
Package Length	3.9 in [10.0 cm]
Package Width	3.9 in [10.0 cm]
Package Height	2.4 in [6.0 cm]

Shipping (Package) 6.0 oz [170.0 g]
Weight

What's in the Box

Included in Package 1 - 4 x 15ft Roll of Hook-and-Loop Cable Tie

**Product appearance and specifications are subject to change without notice.*

