

25ft Hook and Loop Roll - Cut-to-Size Reusable Cable Ties - Bulk Industrial Wire Fastener Tape /Adjustable Fabric Wraps Red / Resuable Self Gripping Cable Management Straps (HKLP25RD)

Product ID: HKLP25RD



This 25 ft. roll of hook and loop roll tape makes it easy to keep your cables neat and tidy by binding them together or binding them to a structure.

This roll of hook and loop fastener straps offers a quick and easy solution for bundling cables together and securing your cables for better routing. Help protect your equipment by reducing cable tension and preventing excessive heat caused by unorganized cables restricting airflow.

You can cut the roll of hook and loop fastener fabric to size using household scissors, meaning you can choose the perfect length for your specific application.

While the most common use for this hook-and-loop fabric is binding and routing cables, you can also use it for other materials in your IT environment such as tools or raceways. The reusable tie wraps are easy to remove and adjustable, avoiding the hassle and waste of traditional zip ties.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

This roll of cable tie is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Keep your office or server room neat and tidy, by binding your equipment cables together

- Prevent damage to your rack-mount equipment by routing cables to improve airflow and reduce port tension

Features

- **VERSATILE USE:** This 25 ft. bulk roll of reusable red hook and loop tape allows you to cut and adjust cable ties to the length you need without the waste of traditional zip ties
- **REDUCE CABLE STRAIN:** This industrial strength hook and loop roll allows you to route cables where needed and relieves strain on connectors that can lead to premature breakage
- **EASY INSTALLATION:** This roll of adjustable fabric hook and loop fastener straps offers a quick and easy solution for fastening cables together and securing your cables
- **PROTECT EQUIPMENT:** Proper cable management using these self gripping electrical wire hooks and loops improves airflow around equipment and reduces cable strain
- **THE STARTECH.COM ADVANTAGE:** 2-year warranty, free lifetime technical support. Available in different colors for easy visual cable identification

Environmental

| | |
|-----------------------|--------------------------|
| Warranty | 2 Years |
| Operating Temperature | 14F to 176F (-10C - 80C) |
| Storage Temperature | 14F to 176F (-10C - 80C) |

Physical Characteristics

| | |
|-------------------|------------------|
| Color | Red |
| Material | Steel |
| Product Length | 25.0 ft [7.6 m] |
| Product Width | 0.7 in [19.0 mm] |
| Product Height | 0.1 in [2.4 mm] |
| Weight of Product | 4.5 oz [127.2 g] |

Packaging Information

| | |
|----------------|------------------|
| Package Length | 7.4 in [18.7 cm] |
| Package Width | 8.4 in [21.4 cm] |
| Package Height | 0.8 in [20 mm] |



| | |
|------------------------------|------------------|
| Shipping (Package) Weight | 4.8 oz [136.3 g] |
|------------------------------|------------------|

**What's in the
Box**

| | |
|---------------------|---|
| Included in Package | 25 foot roll of hook-and-loop cable tie red |
|---------------------|---|

****Product appearance and specifications are subject to change without notice.***

