

5.25 to 3.5 Hard Drive Hot Swap Bay - For 3.5" SATA/SAS Drives - Trayless

Product ID: HSB13SATSASB



This removable hard drive hot-swap bay makes it easy to swap 3.5" SATA or SAS drives in and out of your server or desktop computer, using an available 5.25" front drive bay. It features a trayless design that saves you installation time and enables you to insert or remove drives as needed. With its durable plastic and aluminum construction, it provides a cost-effective solution for drive maintenance and interchangeability of data between multiple systems.

This hot-swap bay/mobile rack is ideal for IT professionals, such as system administrators or computer operators, for quickly swapping drives.

With support for both SATA and SAS 3.5" drives, it saves valuable time in environments where storage drives need to be replaced or removed regularly, such as in server rooms and data centers. Its cost-effective design makes it ideal for large deployments of system builds or upgrades, and for organizations intent on maximizing their IT budget spend.

The removable hard drive hot-swap bay provides a protective backplane with a lightweight yet durable plastic and aluminum housing. To safeguard your data, you can lock the drive bay door to prevent you from unintentionally disconnecting the drive.

To maximize the speed and performance of your drives, the mobile rack supports SAS I and II and SATA I, II and III, providing data transfer speeds up to 6Gbps when paired with a compatible controller.

The HSB13SATSASB is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Provides a cost-effective solution for building or upgrading computer systems for organizations such as government agencies, small-to-medium businesses, educational institutions, medical facilities, and military organizations

- Provides easy hot-swapping of drives in environments where drives need to be replaced or removed regularly, such as server rooms and data centers
- Ideal for industrial or enterprise storage applications such as data backup, recovery, and archiving

Features

- Hot swap drives between systems, using a 3.5" SATA or SAS drive in a 5.25" front bay
- Durable plastic and aluminum construction
- Trayless design for ease of use
- Supports SAS I/II and SATA I/II/III
- Lockable, secure drive door
- Venting to optimize heat dissipation

Hardware

Warranty	2 Years
Front Door Key Lock	Yes
Fan(s)	No
Interface	SATA
Number of Drives	1
Drive Size	3.5in
Compatible Drive Types	SAS & SATA
Drive Installation	Removable

Performance

Maximum Data Transfer Rate	6 Gbps
Type and Rate	SATA/SAS 6 Gbps
Max Drive Capacity	Currently tested with up to 10TB 7200 RPM hard drive
Hot Swap Capability	Yes
MTBF	50,000 cycles
Temperature Alarm	No



Connector(s)

Drive Connectors	29 pin SAS SFF-8482 Female
Host Connectors	SATA Data & Power Combo (7+15 pin)

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Indicators

LED Indicators	Drive Power/Activity
----------------	----------------------

Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-20C to 60C(-4F to 140F)
Humidity	Operating - 5~85% RH Non-condensing Storage - 5~95%

Physical Characteristics

Color	Black
Material	Plastic and Aluminum
Max Drive Height	1.0 in [26.1 mm]
Product Length	7.2 in [18.4 cm]
Product Width	5.8 in [14.8 cm]
Product Height	1.7 in [42.0 mm]
Weight of Product	10.9 oz [308.0 g]

Packaging Information

Package Length	8.1 in [20.5 cm]
Package Width	6.0 in [15.3 cm]
Package Height	2.0 in [50.0 mm]
Shipping (Package) Weight	16.1 oz [456.0 g]



**What's in the
Box**

Included in Package	
	mobile rack
	keys
	backplane-mounting screws
	SATA/SAS data cable
	Molex to SATA and LED cable
	SATA to SATA and LED cable
	quick-start guide

****Product appearance and specifications are subject to change without notice.***

