

## 5.25 to 3.5 Hard Drive Hot Swap Bay - For 3.5" SATA/SAS Drives - Trayless - Aluminum

Product ID: HSB1SATSASBA



This removable hard drive hot-swap bay makes it easy to swap 3.5" SATA or SAS drives in and out of your server or desktop computer, using an available 5.25" front drive bay. It features a trayless design that saves you installation time and enables you to insert or remove drives as needed, creating a convenient solution for drive maintenance and interchangeability of data between multiple systems.

This hot-swap bay/mobile rack is ideal for IT professionals, such as system administrators or computer operators, for quickly swapping, replacing, or transporting drives between various systems and locations. With support for both SATA and SAS 3.5" drives, it saves valuable time in environments where storage drives need to be replaced or removed regularly, such as in server rooms and data centers.

The hot-swap bay provides a protective backplane with a durable aluminum housing that offers ventilation to ensure proper air flow and heat dissipation. To safeguard your data, you can lock the drive bay door to prevent unauthorized access to your drive.

To maximize the speed and performance of your drives, the mobile rack supports SAS I and II and SATA I, II and III, providing data transfer speeds up to 6Gbps when paired with a compatible controller.

The HSB1SATSASBA is backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Provides easy hot-swapping of drives in environments where drives need to be replaced or removed regularly, such as server rooms and data centers

- Ideal for use in industrial or enterprise storage applications such as data backup, recovery, and archiving
- For building or upgrading computer systems for organizations such as government agencies, small-to-medium businesses, educational institutions, medical facilities, and military organizations

## Features

- Hot swap drives between systems, using a 3.5" SATA or SAS drive in a 5.25" front bay
- Durable aluminum construction
- Trayless design for ease of use
- Supports SAS I/II and SATA I/II/III
- Lockable, secure drive door
- Venting to optimize heat dissipation

<b>Hardware</b>	Warranty	2 Years
	Front Door Key Lock	Yes
	Fan(s)	No
	Interface	SATA
	Number of Drives	1
	Drive Size	3.5in
	Compatible Drive Types	SAS & SATA
	Drive Installation	Removable
<b>Performance</b>	Maximum Data Transfer Rate	6 Gbps SATA/SAS 6 Gbps
	Type and Rate	Currently tested with up to 10TB 7200 RPM hard drive
	Max Drive Capacity	Yes
	Hot Swap Capability	No
	Temperature Alarm	
<b>Connector(s)</b>	Drive Connectors	29 pin SAS SFF-8482 Female
	Host Connectors	SATA Data & Power Combo (7+15 pin)
<b>Software</b>	OS Compatibility	OS independent; No software or drivers required
<b>Indicators</b>	LED Indicators	Drive Power/Activity
<b>Environmental</b>	Operating Temperature	0C to 50C (32F to 122F)
	Storage Temperature	-20C to 60C(-4F to 140F)
	Humidity	Operating - 5~85% RH Non-condensing

Storage - 5~95%

---

<b>Physical Characteristics</b>	Color	Black
	Material	Aluminum
	Max Drive Height	1.0 in [26.1 mm]
	Product Length	7.1 in [1.8 cm]
	Product Width	5.7 in [1.5 cm]
	Product Height	1.5 in [39.000 mm]
	Weight of Product	11.9 oz [336.000 g]

---

<b>Packaging Information</b>	Package Length	7.8 in [2.0 cm]
	Package Width	5.9 in [1.5 cm]
	Package Height	1.8 in [45.000 mm]
	Shipping (Package) Weight	14.5 oz [412.000 g]

---

<b>What's in the Box</b>	Included in Package	backplane
	Included in Package	keys
	Included in Package	screws
	Included in Package	quick-start guide
	Included in Package	SATA data cable

---

***\*Product appearance and specifications are subject to change without notice.***

