

3 Drive 3.5in Trayless Hot Swap SATA Mobile Rack Backplane

Produkt ID: HSB320SATBK



This 3 Bay SATA Mobile Rack lets you swap between 3.5in SATA hard drives in seconds.

A time saving storage solution, the mobile rack offers three trayless SATA hard drive bays, allowing you to hot swap Serial ATA hard drives but avoid having to mount the drives to trays for deployment or unfasten them for replacement.

To maximize performance and utilize the full speed potential of your SATA III hard drives, this HDD Backplane supports SATA III for transfer speeds up to 6 Gbps when paired with a compatible controller.

Supporting up to three hard drives, the mobile SATA hot swap rack only takes up two 5.25in drive bays inside a host computer - maximizing space-efficiency within the computer. With support for SATA HDD speeds up to 6.0 Gbps, the mobile rack/backplane is fully compatible with RAID installations to ensure maximum performance and versatility for enhanced storage applications.

Using Terabyte hard drives? Don't expose your Hard Drive and valuable data to unnecessary heat!

The HSB320SATBK has two built-in 40mm fans that re-distribute the heat build-up generated as a result of typical drive operation. This feature is especially important for larger volume storage drives, and faster "spinning" drives (i.e 7200 RPM), as it can help optimize drive operability and in turn preserve stored data integrity.

Certifikat, rapporter och kompatibilitet





Användning

- High-end workstations
- Imaging - For System Builders or configuring new systems - Use Hot Swap Bay in master system to copy Windows OS quickly to multiple blank hard drives as part of system building process
- IT environments where just need to quickly insert/replace removable hard drive - no protection required for mobility reasons for hard drive
- Serial ATA servers and storage subsystems
- Serial ATA Drive Arrays
- Network Attached Storage
- Enterprises replacing IDE/Parallel ATA hard drives with SATA hard drives

Funktioner

- Holds up to three SATA drives across two 5.25" bays
- Trayless design: drives are not mounted into separate trays/enclosures
- Internal rubber shock absorbers
- Solid aluminum construction
- 10,000+ insertion rating
- Power and Activity LEDs for each drive
- Support for SATA revision I/II/III (1.5/3.0/6.0 Gbps)
- Supports 3.5" form factor SATA hard drives
- Plug-and-Play and Hot-Swap compatible

Hårdvara

Garantipolicy	2 Years
Flaktar	2 - 40 mm

	Antal enheter	3
	Enhetsstorlek	3.5in
	Enhetsstyp	SATA
<hr/>		
Prestanda	Bullernivå	24 dBA
	Hot swap-förmåga	Ja
	Inläkningshastighet	10, 000+ Cycles
<hr/>		
Kontakt(er)	Enhetskontakter	3 - SATA (7-stifts, data) 3 - SATA-ström (15-stifts)
	Värdkontakter	3 - SATA (7-stifts, data) 3 - SATA-ström (15-stifts)
<hr/>		
Mjukvara	OS-kompatibilitet	OS independent; No software or drivers required
<hr/>		
Indikatorer	LED-indikatorer	3 - Drive Power 3 - Drive Activity
<hr/>		
Miljö	Drifttemperatur	0°C to 50°C (32°F to 122°F)
	Förvaringstemperatur	0°C to 50°C (32°F to 122°F)
	Luftfuktighet	Operating - 5~85% RH Non-condensing Storage - 5~95%
<hr/>		
Utseende	Färg	Svart
	Kabinetttyp	Aluminium och plast

Produktlängd	7.6 in [19.4 cm]
Produktbredd	5.7 in [14.6 cm]
Produkthöjd	3.3 in [8.5 cm]
Produktvikt	2.4 lb [1.1 kg]

Förpackning

Paketets längd	10.6 in [26.8 cm]
Paketets bredd	5.6 in [14.3 cm]
Paketets höjd	8.6 in [21.8 cm]
Fraktvikt (förpackning)	3.6 lb [1.6 kg]

Vad det är i lådan

Ingår i paketet	1 - 5.25" Tray-Less SATA Hot-Swap Bay
	3 - SATA to LP4 Molex + LED Cable
	3 - SATA cable
	1 - Screw kit
	1 - Instruction Manual

Warranty Information

Warranty	2 År
----------	------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.