

15ft (4.5m) Heavy Duty Extension Cord, NEMA 5-15R to NEMA 5-15P Black Extension Cord, 15A 125V, 14AWG, Heavy Gauge Extension Power Cable, NEMA 5-15R to NEMA 5-15P AC Power Cord

Product ID: HX-15F-POWER-CORD



The HX-15F-POWER-CORD is a NEMA 5-15P to NEMA 5-15R power extension cable which features heavy gauge wire (14 AWG) that is suitable for handling 125V at 15A, making it a reliable solution for connecting larger servers to PDUs (Power Distribution Units).

This 15ft power extension cable extends your existing power connection, enabling the use of a PC or powered device.

HX-15F-POWER-CORD is backed for life, including free lifetime 24/5 multi-lingual technical assistance.

Certifications, Reports and Compatibility



Applications

Features

- **HEAVY DUTY EXTENSION CABLE:** This 15ft (4.5m) 14AWG universal power cord with NEMA 5-15P and NEMA 5-15R connectors is suitable for workstations/home offices Indoor use only Rated to carry 125V at 15A
- **PERFORMANCE AND SAFETY:** UL listed components Fully molded strain relief on connectors for durability Fire Rating: VW-1 3 Conductor Power Cable with 100% copper wire Available in 6ft and 10ft

- **SPECS:** 15ft (4.5m) AC Power Cord NEMA 5-15P to NEMA 5-15R 14AWG 125V 15A (Max) Jacket Type: SJT Jacket Material: PVC Color: Black Temperature Range: 14 to 95F (-10 to 35C) Cable Outer Diameter: 0.36in (9.25mm)
- **COMPATIBILITY:** NEMA 5-15 PC Power Cord works with 3 prong North American plugs and receptacles Extend power connections to servers, desktop computers, monitors, printers, and more Replacement power extension cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this power extension cable is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Number of Conductors	3
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	VW-1 Rated
Cable Type	SJT

Connector(s)

Connector A	1 - NEMA 5-15 Power (North America)
Connector B	1 - NEMA 5-15 Power (North America)

Power

Input Voltage	125 AC
Input Current	15 A

Environmental

Operating Temperature	-10 to 35C (14 to 95F)
Storage Temperature	-15 to 70C (5 to 158F)
Humidity	5% ~ 95%

Physical Characteristics

Color	Black
Cable Length	15.0 ft [4.6 m]

Cable OD	0.4 in [9.2 mm]
Product Length	1.0 in [2.5 cm]
Product Width	180.1 in [457.5 cm]
Product Height	1.4 in [3.5 cm]
Weight of Product	1.5 lb [0.7 kg]

Packaging Information

Package Quantity	1
Package Length	5.7 in [14.5 cm]
Package Width	11.4 in [29.0 cm]
Package Height	2.0 in [5.0 cm]
Shipping (Package) Weight	1.6 lb [0.7 kg]

What's in the Box

Included in Package	1 - Power Extension Cable
---------------------	---------------------------

****Product appearance and specifications are subject to change without notice.***