

## 24in Internal USB Motherboard Header to Parallel Adapter

Produkt ID: ICUSB1284INT



The ICUSB1284INT Internal USB Motherboard Header to Parallel Adapter lets you add a parallel port to any standard or low-profile/half-height desktop system that is equipped with an available USB motherboard header, offering data transfer rates up to 1.5Mbps.

Unlike standard USB to parallel cables, this cable is designed for use inside the PC case, affording an entirely internal solution with no mess or extra adapters needed.

This compact and simple USB adapter offers a cost-effective solution that bridges the compatibility gap between modern computers and legacy parallel peripherals.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifikat, rapporter och kompatibilitet

### Användning

- Quickly add a parallel port to your computer for use with printers utilizing DB25 connectors
- Perfect for system builders looking to add legacy functionality to newer motherboards that lack an integrated parallel port

### Funktioner

- Fully automatic, high speed bi-directional parallel port

- 512 Bytes dynamically allocated unified data buffer for upstream and downstream data transfer
- Standard profile full-height bracket installed
- Includes optional low profile/half-height bracket
- On-chip transceivers and regulator for USB interface
- Full compliance with IEEE 1284-1994
- Bus-Powered – no separate power supply or battery required
- USB 1.1 compatible

---

#### Hårdvara

Garantipolicy	2 Years
Portar	1
Gränssnitt	Parallell
Busstyp	Moderkortskontakt
Korttyp	Standardprofil (inkl. LP-fäste)
Porttyp	Inbyggd på kort
Industristandarder	IEEE 1284
Chipset-ID	Prolific - PL2305

---

#### Prestanda

Maximal dataöverföringshastighet	1.5Mbps
----------------------------------	---------

---

#### Kontakt(er)

Interna portar	IDC (10-stifts, moderkortskontakt)
Externa portar	DB-25 (25-stifts, D-Sub)

---

#### Mjukvara

OS-kompatibilitet	Windows® 98SE, ME, 2000, XP, Vista, 7, 8, 8.1, 10 Windows Server® 2000, 2003, 2008 R2, 2012, 2012 R2, 2016
-------------------	---



Mac OS X® 10.6 to 10.12

Linux 2.6.x to 4.11.x <i>LTS Versions only</i>

Microsoft  
WHQL-certifierad Ja

---

Miljö

Drifttemperatur 0°C to 115°C (32°F to 239°F)

Förvaringstemperatur -55°C to 150°C (-67°F to 302°F)

---

Utseende

Kabellängd 24.0 in [61 cm]

Produktlängd 1.6 in [40 mm]

Produktbredd 2.1 in [53 mm]

Produkt höjd 6.9 in [17.6 cm]

Produktvikt 1.9 oz [55 g]

---

Förpackning

Package Length 8.3 in [21 cm]

Package Width 5.7 in [14.5 cm]

Package Height 1.6 in [40 mm]

Fraktvikt (förpackning) 4.6 oz [130 g]

---

Vad det är i lådan

Ingår i paketet USB header to Parallel Adapter

Low profile bracket

Driver CD

Instruction Manual

---

\* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

