

## 24in Internal USB Motherboard Header to Parallel Adapter

**Product ID:** ICUSB1284INT



The ICUSB1284INT Internal USB Motherboard Header to Parallel Adapter lets you add a parallel port to any standard or low-profile/half-height desktop system that is equipped with an available USB motherboard header, offering data transfer rates up to 1.5Mbps.

Unlike standard USB to parallel cables, this cable is designed for use inside the PC case, affording an entirely internal solution with no mess or extra adapters needed.

This compact and simple USB adapter offers a cost-effective solution that bridges the compatibility gap between modern computers and legacy parallel peripherals.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Perfect for system builders looking to add legacy functionality to newer motherboards that lack an integrated parallel port
- Quickly add a parallel port to your computer for use with printers utilizing DB25 connectors

### Features

- Bus-Powered – no separate power supply or battery required
- On-chip transceivers and regulator for USB interface

- Full compliance with IEEE 1284-1994
- USB 1.1 compatible
- Fully automatic, high speed bi-directional parallel port
- 512 Bytes dynamically allocated unified data buffer for upstream and downstream data transfer
- Includes optional low profile/half-height bracket
- Standard profile full-height bracket installed

---

#### Hardware

Warranty	2 Years
Ports	1
Interface	Parallel
Bus Type	Motherboard Header
Card Type	Standard Profile (LP bracket incl.)
Port Style	Integrated on Card
Industry Standards	IEEE 1284
Chipset ID	Prolific - PL2305

---

#### Performance

Maximum Data Transfer Rate	1.5Mbps
----------------------------	---------

---

#### Connector(s)

Internal Ports	IDC (10 pin, Motherboard Header)
External Ports	DB-25 (25 pin, D-Sub)

---

#### Software

OS Compatibility	Windows 98SE, ME, 2000, XP, Vista, 7, 8, 8.1, 10 Windows Server 2000, 2003, 2008 R2, 2012, 2012 R2, 2016 Mac OS X 10.6 to 10.12 Linux 2.6.x to 4.11.x <i>LTS Versions only</i>
Microsoft WHQL Certified	Yes

---

## Environmental

Operating Temperature	0C to 115C (32F to 239F)
Storage Temperature	-55C to 150C (-67F to 302F)

---

## Physical Characteristics

Cable Length	24.0 in [61 cm]
Product Length	1.6 in [40 mm]
Product Width	2.1 in [53 mm]
Product Height	6.9 in [17.6 cm]
Weight of Product	1.9 oz [55 g]

---

## Packaging Information

Package Length	8.3 in [21 cm]
Package Width	5.7 in [14.5 cm]
Package Height	1.6 in [40 mm]
Shipping (Package) Weight	4.6 oz [130 g]

---

## What's in the Box

Included in Package	Driver CD
	Instruction Manual
	USB header to Parallel Adapter
	Low profile bracket

---

***\*Product appearance and specifications are subject to change without notice.***

