

3 ft 1s1p USB to Serial Parallel Port Adapter Cable

Product ID: ICUSB2321284



The ICUSB2321284 1S1P USB to Serial/Parallel Adapter Cable enables you to connect DB9 RS232 serial devices and IEEE 1284 parallel devices to your PC or Linux laptop or desktop computer, through a single USB port, as though the computer offered onboard connectors.

An innovative solution, the adapter cable features both a parallel and serial port that can be used simultaneously, delivering serial and parallel data rates of up to 921.6 Kbps and 1Mbps (respectively) to ensure optimum performance from your connected devices.

Simple to install and use, the serial/parallel USB adapter is a cost-effective solution that bridges the connectivity gap between modern computers and legacy serial peripherals.

Backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Connect a satellite receiver, serial modem, or PDA with serial sync
- Connect bar code scanners, receipt printers and other point of sale devices
- Connect, monitor and control industrial/automotive sensors and equipment
- Perfect for IT Administrators looking to add legacy functionality to newer laptops, desktops and servers that lack integrated RS-232 Serial and/or Parallel ports
- Connect to console ports, UPS, and other devices in the server room/server closet

Features

- Compatible with modems, printers, bar code scanners, servers, PDUs, and most other serial RS232 or Parallel equipment
- Easy to setup and install - plug and play for most operating systems
- No external power needed - draws power from the USB connection
- Supports serial baud rates of up to 921.6 Kbps
- Thin, lightweight design

Hardware

Warranty	3 Years
Ports	2
Interface	Serial
Bus Type	USB 2.0
Port Style	Cable Adapters
Industry Standards	RS232, IEEE 1284, USB 1.1
Chipset ID	ASIX - MCS7715


Performance

Serial Protocol	RS-232
Max Baud Rate	921.6 Kbps
Data Bits	5, 6, 7, 8
FIFO	192 Bytes
Parity	Even, Odd, Mark, Space, None

Connector(s)

Connector Type(s)	DB-9 (9 pin, D-Sub)
	DB-25 (25 pin, D-Sub)
	USB Type-A (4 pin) USB 2.0

Software



OS Compatibility	Windows CE 5.0, XP, Vista, 7, 8, 8.1, 10 Windows Server 2003, 2008 R2, 2012, 2016, 2019 Linux 3.5.x to 4.11.x <i>LTS Versions only</i>
------------------	--

Environmental

Operating Temperature	0C to 60C (32F to 140F)
Storage Temperature	-20C to 80C (-4F to 176F)
Humidity	0~65% RH

Physical Characteristics

Color	Black
Material	Plastic
Cable Length	36.0 in [91.5 cm]
Product Length	39.4 in [100 cm]
Weight of Product	2.4 oz [69 g]

Packaging Information

Package Length	5.6 in [14.3 cm]
Package Width	6.9 in [17.5 cm]
Package Height	1.3 in [32 mm]
Shipping (Package) Weight	4.0 oz [114 g]

What's in the Box

Included in Package	USB to Serial & Parallel cable User Manual
---------------------	---

****Product appearance and specifications are subject to change without notice.***

