

## 2 Port Industrial Wall Mountable USB to Serial Adapter Hub with DIN Rail Clips

**Product ID:** ICUSB2322I



The ICUSB2322I 2-Port Industrial USB to Serial Hub with DIN Rail Clips converts a single USB port into two RS232 serial ports, enabling you to connect to, monitor and control your serial devices.

Featuring rugged metal construction, with sturdy wall-mounting brackets and top-hat DIN Rail clips (included), this USB to Serial Hub provides versatile mounting options and a robust solution for both harsh industrial environments and simple desktop installations.

This USB powered adapter also retains assigned serial COM port values once connected, allowing the same values to be automatically reassigned to the ports provided by the adapter.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Perfect for IT Administrators looking to add legacy functionality to newer notebooks, PCs and servers that lack an integrated RS232 port
- Connect, monitor and control industrial/automotive sensors and equipment
- Connect bar code scanners, receipt printers and other point of sale devices
- Connect a satellite receiver, serial modem, or PDA with serial sync
- Connect and program LED and Digital signage boards with serial communication ports

## Features

- 2-port USB to RS232 serial adapter
- Rugged metal construction
- Wall-mountable, with included DIN Rail clips
- COM retention: COM Port assignments maintained across reboot
- Baud Rate up to 921.6 Kbps
- Powered by an available USB port - no external power adapter required

---

### Hardware

Warranty	2 Years
Ports	2
Interface	Serial
Bus Type	USB 2.0
Port Style	External Hub
Chipset ID	FTDI - FT232RL

---

### Performance

Serial Protocol	RS-232
Max Baud Rate	921.6 Kbps
Data Bits	7, 8
FIFO	256 Bytes
Parity	Odd, Even, Mark, Space, None

Stop Bits 1, 2

---

**Connector(s)**

External Ports 2 - DB-9 (9 pin, D-Sub)  
1 - USB B (4 pin)

---

**Software**

OS Compatibility Windows CE (4.2, 5.0, 6.0), XP Embedded, 98SE, 2000, XP, Vista, 7, 8, 8.1, 10, 11  
Windows Server 2003, 2008 R2, 2012, 2012 R2, 2016, 2019, 2022  
macOS 10.6 to 10.15, 11.0, 12.0, 13.0  
Linux Kernel 3.0.x and up - *<i>LTS Versions only</i>*

---

**Indicators**

LED Indicators 2 - Each, Tx/Rx Activity indicators

---

**Power**

Power Source USB-Powered  
Input Voltage 5V DC  
Plug Type M

---

**Environmental**

Operating Temperature 0C to 55C (32F to 131F)  
Storage Temperature -20C to 85C (-4F to 185F)  
Humidity 5~95% RH

---

**Physical Characteristics**

Color Black  
Material Steel  
Cable Length 6.0 ft [1.8 m]  
Product Length 4.1 in [10.4 cm]  
Product Width 2.6 in [66 mm]  
Product Height 0.9 in [2.4 cm]

Weight of Product 5.7 oz [162 g]

---

**Packaging Information**

Package Quantity 1

Package Length 8.4 in [21.4 cm]

Package Width 5.7 in [14.5 cm]

Package Height 1.6 in [41 mm]

Shipping (Package) Weight 0.8 lb [0.4 kg]

---

**What's in the Box**

Included in Package

- 1 - USB to RS-232 Serial Adapter
- 1 - DIN rail kit
- 1 - 6 ft USB A to B cable
- 1 - Driver CD
- 1 - Instruction Manual

---

***\*Product appearance and specifications are subject to change without notice.***