

2 Port Wall Mountable USB to Serial Adapter Hub with COM Retention

Produkt ID: ICUSB2322X



The ICUSB2322X 2 Port Professional Grade USB Serial Adapter converts a single USB port to two RS232 serial ports allowing you to connect to, monitor and control your serial devices. Rugged metal construction and sturdy wall-mount brackets provide a robust solution for both harsh industrial environments and simple desktop installations.

Powered by USB, the device does not require a power outlet for most standard applications. For installations requiring more power through the RS232 ports, the hub supports connection of an external power adapter (not included) to the integrated DC jack or terminal block. Once connected, the adapter retains assigned serial COM port values, allowing the same values to automatically be re-assigned to the ports provided by the adapter in the event it is disconnected, then re-connected to the host computer.

This innovative Serial adapter offers a professional grade solution for connecting legacy or industrial RS232 serial devices to more modern computers, or computers with unused USB ports – perfect for connecting serial modems, barcode scanners or any device with serial sync through USB, eliminating the expense of upgrading serial peripherals for USB compatibility.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifikat, rapporter och kompatibilitet





Användning

- Perfect for IT Administrators looking to add legacy functionality to newer notebooks, PCs and servers that lack an integrated RS232 port
- Connect, monitor and control industrial/automotive sensors and equipment
- Connect bar code scanners, receipt printers and other point of sale devices
- Connect a satellite receiver, serial modem, or PDA with serial sync
- Connect and program LED and Digital signage boards with serial communication ports

Funktioner

- 2-port USB to RS232 serial adapter
- Rugged metal construction
- Wall-mountable
- COM Port assignments maintained across reboot
- Baud Rate up to 230 Kbps
- Optional DC jack or terminal block power connections
- Powered by an available USB port - no external power adapter required
- Designed to make serial port expansion quick and simple
- Provides dual buffers for upstream and downstream data transfer
- Supports automatic handshake mode
- Enables and disables enumerations

Hårdvara

Garantipolicy	2 Years
Portar	2

	Gränssnitt	Seriell
	Busstyp	USB 2.0
	Porttyp	Extern hubb
	Chipset-ID	Texas Instruments - TIUSB3410
Prestanda	Seriellt protokoll	RS-232
	Maximal överföringshastighet	230,4 kbps
	FIFO	32 Bytes
Kontakt(er)	Kontakttyp(er)	1 - USB B (4-stifts)
	Externa portar	2 - DB-9 (9-stifts, D-Sub)
Mjukvara	OS-kompatibilitet	Windows® XP, Vista, 7, 8, 8.1, 10, 11 Windows Server® 2003, 2008 R2, 2012 Note: Windows 8.1 - 10 is only supported by REV 2
Ström	Strömkälla	Medföljer ej (behövs ej vid vanlig användning)
	Inspänning	9 ~ 36 DC
	Kontakttyp	N
Miljö	Drifttemperatur	-10°C to 80°C (14°F to 176°F)
	Förvaringstemperatur	-20°C to 100°C (-4°F to 212°F)
	Luftfuktighet	5~85% RH
Utseende	Färg	Svart
	Kabinetttyp	Stål

Produktlängd	4.4 in [11.3 cm]
Produktbredd	3.1 in [8.0 cm]
Produkthöjd	0.9 in [2.3 cm]
Produktvikt	10.6 oz [300.0 g]

Förpackning

Förpackningsantal	1
Paketets längd	8.0 in [20.3 cm]
Paketets bredd	5.6 in [14.3 cm]
Paketets höjd	1.7 in [4.2 cm]
Fraktvikt (förpackning)	15.9 oz [450.0 g]

Vad det är i lådan

Ingår i paketet	1 - USB to RS-232 Serial Adapter
	1 - 3ft USB A to B cable
	1 - Instruction Manual

Warranty Information

Warranty	2 År
----------	------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.