

USB to RS232 DB9 Serial Adapter Cable - M/M

Product ID: ICUSB232



The StarTech.com ICUSB232 1ft USB to DB9 RS232 Serial Adapter Cable lets you connect DB9 RS232 serial devices to your Mac or PC laptop or desktop computer through a USB port, as though the computer offered an onboard DB9M connector.

A cost-effective solution that bridges the compatibility gap between modern computers and legacy serial peripherals, as well as offering compatibility with nearly all PLC Brands (AllenBradley, Siemens, Modicon, Servos, Indramat, Siemens, AB, etc.).

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Perfect for IT Administrators looking to add legacy functionality to newer notebooks, PCs and servers that lack an integrated RS232 port
- Connect a satellite receiver, serial modem, or PDA with serial sync
- Connect bar code scanners, receipt printers and other point of sale devices
- Connect, monitor and control industrial/automotive sensors and equipment
- Connect and program LED and Digital signage boards with serial communication ports
- Compatible with nearly all PLC Brands (AllenBradley, Siemens, Modicon, Servos, Indramat, Siemens, AB, etc.)

Features

- Easy to setup and install
- Compatible with all popular PDAs, modems, printers, bar code scanners, etc.
- Thin cables and light weight makes it portable and easy to carry
- No external power needed - draws power from the USB connection
- Supports serial data transfer rates of up to 1 Mbits/sec
- USB to Straight-Through RS232 Serial Adapter

Hardware

Warranty	2 Years
Ports	1
Interface	Serial
Bus Type	USB 2.0
Port Style	Cable Adapters
Industry Standards	USB 1.1/2.0 RS232
Chipset ID	Prolific - PL2303

Performance

Serial Protocol	RS-232
Max Baud Rate	921.6 Kbps
FIFO	192 Bytes

Connector(s)

Connector Type(s)	USB Type-A (4 pin) USB 2.0 DB-9 (9 pin, D-Sub)
-------------------	---

Software

OS Compatibility	Windows 10 (32/64bit), 8 / 8.1 (32/64), 7 (32/64), Vista (32/64), XP (32/64), 2000, ME, 98SE, CE 4.2, 5.2 Windows Server 2012, 2008 R2, 2003 macOS 10.x, 11.0 (Tested up to 11.0)
------------------	---

Linux 2.4.x - 3.9.x

Environmental

Operating Temperature	0C to 60C (32F to 140F)
Storage Temperature	-20C to 80C (-4F to 176F)
Humidity	0~65% RH

Physical Characteristics

Material	Plastic
Cable Length	12.0 in [30.5 cm]
Product Length	14.6 in [37 cm]
Product Width	1.3 in [34 mm]
Product Height	0.7 in [18 mm]
Weight of Product	2.9 oz [81.6 g]

Packaging Information

Package Length	4.1 in [10.5 cm]
Package Width	1.4 in [36 mm]
Package Height	8.4 in [21.4 cm]
Shipping (Package) Weight	3.2 oz [90 g]

What's in the Box

Included in Package	USB to Serial Converter
	User Manual

****Product appearance and specifications are subject to change without notice.***

