

24in Internal USB Motherboard Header to 2 Port Serial RS232 Adapter - TAA

Produkt ID: ICUSB232INT2



The ICUSB232INT2 USB to Serial Adapter lets you add 2 RS232 ports to any desktop system that is equipped with an available USB motherboard header.

Unlike standard USB to serial cables, this cable is designed for use inside the PC case, affording an entirely internal solution with no mess or extra adapters needed.

This compact and simple USB adapter offers a cost-effective solution that bridges the compatibility gap between modern computers and legacy serial peripherals.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifikat, rapporter och kompatibilitet



Användning

- Perfect for system builders looking to add legacy functionality to newer motherboards that lack an integrated RS232 port
- Connect bar code scanners, receipt printers and other serial devices to an internal USB motherboard header
- Connect, monitor and control industrial/automotive sensors and equipment
- Connect a satellite receiver, serial modem, or PDA with serial sync

Funktioner

- Single chip USB to asynchronous serial data transfer interface
- Supports COM port retention
- Bus Powered – no separate power supply or battery required
- FIFO receive and transmit buffers for high data throughput.
- Synchronous and asynchronous bit bang interface options with RD# and WR# strobes
- UHCI/OHCI/EHCI host controller compatible
- USB 2.0 Full Speed compatible

Hårdvara

Garantipolicy	2 Years
Portar	2
Gränssnitt	Seriell
Busstyp	Moderkortskontakt
Korttyp	Standardprofil (inkl. LP-fäste)
Porttyp	Inbyggd på kort
Chipset-ID	FTDI - FT232RL

Prestanda

Seriellt protokoll	RS-232
Maximal överföringshastighet	115.2 kbps

	Databitar	7, 8
	FIFO	256 Bytes
	Paritet	None, Odd, Even, Space, Mark
	Stoppbitar	1, 2
Kontakt(er)	Interna portar	1 - IDC (10-stifts, moderkortskontakt)
	Externa portar	2 - DB-9 (9-stifts, D-Sub)
Mjukvara	OS-kompatibilitet	Windows® CE (4.2, 5.0, 6.0), XP Embedded, 98SE, 2000, XP, Vista, 7, 8, 8.1, 10, 11, 11 ARM .Windows Server® 2003, 2008 R2, 2012, 2012 R2, 2016, 2019, 2022 .macOS 10.6 till 10.15, 11.0, 12.0, 13.0, 14.0, 15.0 LinuxLinux Kernel 3.0.x och uppåt - Endast LTS-versioner
	Microsoft WHQL-certifierad	Ja
Miljö	Drifttemperatur	-10°C to 80°C (14°F to 176°F)
	Förvaringstemperatur	-20°C to 100°C (-4°F to 212°F)
	Luftfuktighet	5~85% RH
Utseende	Färg	Grön
	Kabinettyp	Stål
	Kabellängd	24.0 in [609.6 mm]
	Produktlängd	2.7 in [6.8 cm]
	Produktbredd	4.7 in [12.0 cm]
	Produkthöjd	0.7 in [1.9 cm]

	Produktvikt	1.4 oz [40.0 g]
Förpackning		
	Förpackningsantal	1
	Paketets längd	6.9 in [17.4 cm]
	Paketets bredd	5.6 in [14.2 cm]
	Paketets höjd	1.3 in [3.3 cm]
	Fraktvikt (förpackning)	5.2 oz [146.0 g]
Vad det är i lådan		
	Ingår i paketet	1 - USB Header to Serial Adapter
		2 - Low profile bracket
		1 - Driver CD
		1 - Instruction Manual
Warranty Information		
	Warranty	2 År

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.