

USB Stereo Audio Adapter External Sound Card with SPDIF Digital Audio and Stereo Mic

Produkt ID: ICUSBAUDIO2D



The ICUSBAUDIO2D External USB Sound Card lets you add an S/PDIF digital audio output and standard 3.5mm analog audio/microphone connections to your system through USB - a convenient way to bypass or replace an internal sound card without having to open the computer case.

For home-theater quality sound, the USB DAC (digital-to-analog converter) offers 96KHz / 24-bit sampling rates for playback, and a 3.5mm S/PDIF port with support for Dolby® Digital 5.1 surround sound (AC3) and DTS® pass-through (Note: 5.1 surround sound is supported in Windows® only).

This versatile USB audio adapter features an integrated 3.5mm 4-position TRRS connection for your headphones or combination headset/microphone. Also a convenient external volume control for quick adjustments, a hardware EQ switch for Bass or Treble boosting, and an LED status bar to display the current sampling rate.

Please note that the microphone input is stereo only.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifikat, rapporter och kompatibilitet



Användning

- Connect your computer to a home theater audio receiver through S/PDIF, without opening the case
- Add digital audio support to an Ultrabook™ or small form factor system with no internal expansion options
- Replace or upgrade the integrated audio on a laptop or portable computer

Funktioner

- 96KHz / 24-bit Hi-Fi USB Audio
- S/PDIF digital output with AC3 (Dolby Digital) and DTS pass-through support
- 5.1 Surround Sound supported (Windows® only)
- 3.5mm headphone/microphone ports
- 4 position TRRS headset with Mic supported
- Hardware volume knob and Bass/Treble boost EQ switch
- LED sample rate indicators
- 16in attached USB cable

Hårdvara

Garantipolicy	2 Years
Busstyp	USB 2.0
Chipset-ID	Cmedia CM6533

Prestanda

Audio-specifikationer	96 KHz / 24-bit Sample Rate
	Approx 91dB SNR (A-weighting)
	16-100ohm Headphone Drive Ability

Kontakt(er)

	Kontakttyp(er)	1 - 3,5 mm Mini-Toslink (SPDIF, optisk)
		1 - 3.5 mm minijack (4-polig)
		1 - 3.5 mm minijack (3-polig)
		1 - USB 2.0 Type-A (4 stift, 480 Mbps)
Mjukvara	OS-kompatibilitet	Windows® XP, Vista, 7, 8, 8.1, 10, 11
		Windows Server® 2003, 2008 R2, 2012, 2012 R2, 2016, 2019, 2022
		Mac OS X® 10.6 to 10.8
		Note: DTS pass-through is supported in Windows 8, 8.1, and 10 only
Särskilda anmärkningar/krav	System- och kabelkrav	Available USB Port
	Obs.	5.1 surround sound output is supported in Windows only
		Mikrofonen är endast stereo.
Indikatorer	LED-indikatorer	1 - Power
		3 - Playback sample rate
Ström	Strömkälla	Strömförsörjd via USB
Miljö	Drifttemperatur	0°C to 60°C (32°F to 140°F)
	Förvaringstemperatur	0°C to 70°C (32°F to 158°F)
	Luftfuktighet	10~90% RH (Non-Condensing)
Utseende	Färg	Svart

Kabinetttyp	Av plast
Kabellängd	16.0 in [406.5 mm]
Produktlängd	1.9 in [47 mm]
Produktbredd	1.8 in [4.6 cm]
Produkthöjd	0.6 in [1.6 cm]
Produktvikt	1.2 oz [33 g]

Förpackning

Förpackningsantal	1
Paketets längd	6.8 in [17.2 cm]
Paketets bredd	5.6 in [14.3 cm]
Paketets höjd	1.3 in [32 mm]
Fraktvikt (förpackning)	3.2 oz [90.0 g]

Vad det är i lådan

Ingår i paketet	1 - USB Stereo Audio Adapter
	1 - Software CD
	1 - Instruction Manual

Warranty Information

Warranty	2 År
----------	------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.