

24in Round ATA 100/133 IDE Cable

Productcode: IDE100RND24



This 24in IDE Drive Cable is designed to fit as a new or replacement hard drive/CD-ROM cable in almost any size of computer case. The cable features a rounded design that can help increase airflow capabilities within the computer case, and provide easier access to internal computer components.

The rounded IDE cable provides two 40-pin female drive connectors, for connecting both a master and slave device to the motherboard IDE bus through a single cable, saving the install space and cost of a second cable.

Providing a cost-effective solution for connecting Ultra ATA 66/100/133 drives, this high quality IDE cable is backed by StarTech.com's Lifetime Warranty.

Certificaties, rapporten en compatibiliteit

Toepassingen

- Rounded IDE cables are used anywhere that flat IDE ribbon cables are required.

Eigenschappen

- Cables take up less area thereby reducing the clutter and allowing for better air flow
- Made of flexible rubber sheathing of various lengths which eliminates the need to relocate devices
- Ultra ATA 66/100/133 80 wire IDE cable

Prestaties

Garantiebeleid	Lifetime
Maximale overdrachtsnelheid	Up to 133Mbps burst transfer rate
Maximale kabellengte	36.0 in [91.4 cm]

Connector(en)

Connector A	IDE (40-polig, EIDE/PATA)
Connector B	IDE (40-polig, EIDE/PATA)

Speciale opmerkingen / vereisten

Notitie	16 and 8 inches between connectors
---------	------------------------------------

Fysieke eigenschappen

Kleur	Grijs
Kabellengte	24.0 in [61.0 cm]
Lengte product	24.0 in [61.0 cm]

Verpakkingsinformatie

Package Length	5.7 in [14.4 cm]
Package Width	1.6 in [40 mm]
Package Height	11.8 in [29.9 cm]
Verzendgewicht (verpakt)	4.2 oz [120 g]

Wat wordt er meegeleverd

Meegeleverd	24in Round ATA 100/133 IDE Cable
-------------	----------------------------------

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.

