

24in Round ATA 100/133 IDE Cable

Produkt ID: IDE100RND24



This 24in IDE Drive Cable is designed to fit as a new or replacement hard drive/CD-ROM cable in almost any size of computer case. The cable features a rounded design that can help increase airflow capabilities within the computer case, and provide easier access to internal computer components.

The rounded IDE cable provides two 40-pin female drive connectors, for connecting both a master and slave device to the motherboard IDE bus through a single cable, saving the install space and cost of a second cable.

Providing a cost-effective solution for connecting Ultra ATA 66/100/133 drives, this high quality IDE cable is backed by StarTech.com's Lifetime Warranty.

Certifikat, rapporter och kompatibilitet



Användning

- Rounded IDE cables are used anywhere that flat IDE ribbon cables are required.

Funktioner

- Cables take up less area thereby reducing the clutter and allowing for better air flow

- Made of flexible rubber sheathing of various lengths which eliminates the need to relocate devices
- Ultra ATA 66/100/133 80 wire IDE cable

Prestanda

Garantipolicy	Lifetime
Maximal dataöverföringshastighet	Up to 133Mbps burst transfer rate
Maximal kabellängd	3.0 ft [0.9 m]

Kontakt(er)

Connector A	1 - IDE (40-stifts, EIDE/PATA)
Connector B	2 - IDE (40-stifts, EIDE/PATA)

Särskilda anmärkningar/krav

Obs.	16 and 8 inches between connectors
------	------------------------------------

Utseende

Färg	Grå
Kabellängd	24.0 in [609.6 mm]
Produktlängd	24.0 in [609.6 mm]

Förpackning

Paketets längd	5.7 in [14.4 cm]
Paketets bredd	1.6 in [40 mm]
Paketets höjd	11.8 in [29.9 cm]
Fraktvikt (förpackning)	0.3 lb [0.1 kg]

Vad det är i lådan

Ingår i paketet	1 - 24in Round ATA 100/133 IDE Cable
-----------------	--------------------------------------

Warranty Information

Warranty	Livslängd
----------	-----------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.