

24in Round ATA 100/133 IDE Cable

Product ID: IDE100RND24



This 24in IDE Drive Cable is designed to fit as a new or replacement hard drive/CD-ROM cable in almost any size of computer case. The cable features a rounded design that can help increase airflow capabilities within the computer case, and provide easier access to internal computer components.

The rounded IDE cable provides two 40-pin female drive connectors, for connecting both a master and slave device to the motherboard IDE bus through a single cable, saving the install space and cost of a second cable.

Providing a cost-effective solution for connecting Ultra ATA 66/100/133 drives, this high quality IDE cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Rounded IDE cables are used anywhere that flat IDE ribbon cables are required.

Features

- Cables take up less area thereby reducing the clutter and allowing for better air flow
- Made of flexible rubber sheathing of various lengths which eliminates the need to relocate devices
- Ultra ATA 66/100/133 80 wire IDE cable

Performance

Warranty	Lifetime
Maximum Data Transfer Rate	Up to 133Mbps burst transfer rate
Maximum Cable Length	36.0 in [91.4 cm]

Connector(s)

Connector A	IDE (40 Pin, EIDE/PATA)
Connector B	IDE (40 Pin, EIDE/PATA)

Special Notes / Requirements

Note	16 and 8 inches between connectors
------	------------------------------------

Physical Characteristics

Color	Gray
Cable Length	24.0 in [61.0 cm]
Product Length	24.0 in [61.0 cm]

Packaging Information

Package Length	5.7 in [14.4 cm]
Package Width	1.6 in [40 mm]
Package Height	11.8 in [29.9 cm]
Shipping (Package) Weight	4.2 oz [120 g]

What's in the Box

Included in Package	24in Round ATA 100/133 IDE Cable
---------------------	----------------------------------

****Product appearance and specifications are subject to change without notice.***

