

HDMI KVM Receiver Over IP Network for the IH2006 Product Series, 4K 60Hz, Driverless, AVoIP, Includes Mounting Kit, Receiver Only

Product ID: IH2006-KVM-RX



The AVoIP KVM Receiver enables remote computer access over an existing TCP/IP network using a keyboard, mouse, and 4K 60Hz HDMI monitor when paired with a compatible transmitter, keeping systems secure from unauthorized access and physical damage.

The plug-and-play design requires no drivers or software and is compatible with all major operating systems, including Windows, macOS, and Linux, as well as hardware platforms like Intel, AMD, Snapdragon/ARM, and Apple Silicon.

Easily expand your setup by adding multiple receivers to create a one-to-many configuration, making it easy to scale with your business needs for flexible and future-proof IP Video or KVM distribution.

Receiver features a durable metal housing with mounting kits for wall or under-desk installation, plus rubber feet for desktop stability. RS232 and 3.5mm audio passthrough ports enable serial and audio extension.

Certifications, Reports and Compatibility



Applications

- Reduce the need for physical access to a computer or server, improving security and efficiency
- Enables secure, high-performance connections between workstations and studio equipment
- Allows operators to manage critical systems from a safe or more convenient location

Features

- **AVoIP KVM RECEIVER:** Pair with an IH2006 transmitter (sold separately) to remotely access and control a computer over a TCP/IP network using a keyboard, mouse, and 4K 60Hz HDMI monitor, providing secure and seamless remote operation
- **SCALABLE EXPANSION:** Easily expand your setup by adding multiple receivers to create a one-to-many configuration, making it easy to scale with your business needs for flexible and future-proof solution
- **NO DRIVERS OR SOFTWARE:** Requires no configuration to get it working; Compatible with any operating system including Windows, macOS and Linux, as well as all hardware platforms such as Intel, AMD, Snapdragon/ARM and Apple Silicon
- **AUDIO & SERIAL EXTENSION:** Equipped with a three-wire RS232 port for serial extension and a 3.5mm audio passthrough port, ensuring seamless transmission of audio and control signals over the network
- **SECURE & FLEXIBLE INSTALLATION:** Durable metal housing with included mounting kit for wall or under-desk installation; Rubber feet prevent slipping for desktop use; Ideal for industrial and professional environments

Hardware

Warranty	2 Years
Audio	Yes
KVM Ports	1
PC Interface	USB
PC Video Type	HDMI
Rack-Mountable	No
Cables Included	No

Performance

On-Screen Display	No
Video Revision	HDMI 2.0
IP Control	Yes
Hot-Key Selection	No

Maximum Digital Resolutions	3840 x 2160 @ 60Hz
Audio Specifications	HDMI - 2 Channel Audio
Port Selection Support	Not Applicable

Connector(s)

Console Interface(s)	2 - USB 2.0 Type-A 1 - Terminal Block (3 Wire) 1 - 3.5mm Stereo Female 3 pos 1 - RJ-45 1 - HDMI
Other Interface(s)	1 - USB Micro-B (5 pin)

Software

OS Compatibility	No Drivers or Software Required
------------------	---------------------------------

Indicators

LED Indicators	1 - Power LED: Solid Blue: Indicates the unit is receiving Power 1 - Sync LED: Off: Transmitter and Receiver have no established a connection Slow Orange Flash: Transmitter and Receiver are connected via Gigabit Ethernet but no Video is transmitting Quick Orange Flash: Transmitter and Receiver are connected via 100Mbps Ethernet but no Video is transmitting Solid Orange: Video is transmitting 1 - KVM LED: Flashing: KVM data is transmitting Solid: Computer and USB Port are connected
----------------	--

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC

Input Current	0.3A
Output Voltage	5 DC
Output Current	2A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	10W

Environmental

Operating Temperature	-20C to 60C (-4F to 140F)
Storage Temperature	-30C to 70C (-22F to 158F)
Humidity	0% ~ 90% RH (non-condensing)

Physical Characteristics

Color	Black
Material	Steel
Product Length	4.2 in [106 mm]
Product Width	4.1 in [103 mm]
Product Height	1.0 in [25 mm]
Weight of Product	10.4 oz [294 g]

Packaging Information

Package Length	5.9 in [14.9 cm]
Package Width	7.8 in [19.9 cm]
Package Height	3.1 in [8.0 cm]
Shipping (Package) Weight	1.1 lb [0.5 kg]

What's in the Box

Included in Package	1 - IP KVM Receiver
	1 - Set of Rubber Feet

1 - RS-232 Terminal Header

1 - Mounting Kit

1 - Universal Power Adapter (NA/UK/EU/ANZ)

**Warranty
Information**

Warranty

2 Years

****Product appearance and specifications are subject to change without notice.***