

12V DC 1.5A Universal Power Adapter

Product ID: IM12D1500P



The IM12D1500P Universal Power Adapter (12V DC, 1.5A) can be used as a replacement or spare AC adapter for many of our products, including , , and . Please see the Accessories section for this product, for a complete list of compatible products.

Backed by a StarTech.com 2-year warranty.

Certifications, Reports and Compatibility

Applications

Features

Power

Warranty	2 Years
Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.8A
Output Voltage	12V DC
Output Current	1.5A

Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	18

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-10C to 60C (14F to 140F)
Humidity	0%~80% RH

Physical Characteristics

Color	Black
Cable Length	4.5 ft [1.4 m]
Product Length	2.8 in [70 mm]
Product Width	2.0 in [50 mm]
Product Height	1.6 in [40 mm]
Weight of Product	5.6 oz [159 g]

Packaging Information

Package Length	5.4 in [13.8 cm]
Package Width	3.6 in [92 mm]
Package Height	2.2 in [57 mm]
Shipping (Package) Weight	7.1 oz [200 g]

What's in the Box

Included in Package	Universal Power Adapter (US/EU/UK)
---------------------	------------------------------------

****Product appearance and specifications are subject to change without notice.***

