

1 Port ISA RS232 Serial Adapter Card with 16550 UART

Productcode: ISA1S550



StarTech.com's ISA-based RS232 Serial Card (16550 UART) can be installed in an ISA motherboard slot to add an RS232 serial COM port, with support for data transfer rates of up to 460.8Kbps for peak serial device performance.

The ISA Serial Adapter Card includes drivers for Windows® 3.1, 95, 98, NT4 and NT5, and offers a full built-in jumper set to ensure easy configuration and broad compatibility.

A cost-effective solution for connecting serial modems, POS devices, PDAs, digital cameras, printers, ISDN terminal adapters and more, to a system, the ISA serial card is backed by StarTech.com's Lifetime Warranty and free lifetime technical support.

Certificaties, rapporten en compatibiliteit



Toepassingen

- **Manufacturing** (CNC machinery, process control equipment, bar code scanners, serial printers)
- **POS** (credit/debit card readers, receipt printers, bar code scanners, cash registers, scales)
- **Consumer** (modems, PDAs, digital cameras, printers)

- **Security** (UPS control, access key panels, video cameras, card readers, modems)
- **Casino** (video lottery terminals, slot machines)
- **Environmental Control** (lighting, temperature, clocks)
- **Healthcare** (patient monitoring equipment, nurses' stations, modems)
- **Hotel Front Desk** (serial printers, bar code scanners, keyboard, mouse, receipt printer, credit/debit card reader)
- **Hospitality/Restaurant** (credit card/debit card reader, serial printers)
- **ISDN Networking**

Eigenschappen

- Includes drivers for Windows® 3.1, 95, 98, NT4, NT5
- Full jumper set to ensure compatibility with almost any PC system
- Supports the RS-232 interface

Hardware

Garantiebeleid	Lifetime
Poorten	1
Interface	Serieel
Bus type	ISA
Kaarttype	Standaard
Poorttype	Geïntegreerd op kaart
Chipsetcode	National Semiconductor - NS16550AFN

Prestaties

Maximale overdrachtsnelheid	460.8 Kbps
Seriële protocol	RS-232
Max. baudrate	460,8 kbit/s

FIFO 16 Bytes

Algemene specificaties COM Settings: COM1 to COM7

Connector(en)

Type connector(en) 1 - ISA (16-bit)

Externe poorten 1 - DB-9 (9-polig, D-Sub)

Gebruiksomgeving

Bedrijfstemperatuur -10°C to 80°C (14°F to 176°F)

Opslagtemperatuur -20°C to 100°C (-4°F to 212°F)

Vochtigheid 5~85% RH

Fysieke eigenschappen

Lengte product 5.0 in [12.8 cm]

Hoogte product 2.8 in [7 cm]

Verpakkingsinformatie

Lengte Verpakking 5.9 in [15 cm]

Package Width 0.9 in [22 mm]

Package Height 5.4 in [13.8 cm]

Verzendgewicht (verpakt) 0.3 lb [0.1 kg]

Wat wordt er meegeleverd

Meegeleverd 1 - I/O CARD

1 - Instruction Sheet

Garantiebepalingen

Warranty Levenslang

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.