

1m External Mini SAS Cable - Serial Attached SCSI SFF-8088 to SFF-8088

Product ID: ISAS88881



The ISAS88881 1m External SAS Cable is designed for high-performance networks, servers, workstations and desktops, supporting data transfer rates of up to 6 Gbps.

This durable Mini SAS cable features SFF-8088 to SFF-8088 plugs for connecting your external SAS devices (controllers, hard drives, SAN storage area network, etc.), and it is TAA-compliant for Federal (GSA Schedule) purchases.

Constructed of high quality materials this 1-meter SAS cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Connect external hard drive to SAS Controller
- For use in Storage Area Networks, to connect SAS Expander enabled controllers and enclosures
- Connect SAS Controllers to SAS Backplanes

Features

- 2x SFF-8088 plugs with latches
- Durable metal connectors
- Supports data transfer rates up to 6 Gbps

- Multi-lane design
- Backwards compatible with SATA devices

Hardware

Warranty	Lifetime
Number of Conductors	8 Twisted Pair
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-polyester foil with tinned copper braid

Connector(s)

Connector A	SFF-8088 (26-pin, External Mini-SAS)
Connector B	SFF-8088 (26-pin, External Mini-SAS)

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	39.4 in [100 cm]
Product Length	39.4 in [100.0 cm]
Product Width	0.0 in [0.0 mm]
Product Height	0.0 in [0.0 mm]
Weight of Product	5.0 oz [143.0 g]

Packaging Information

Package Quantity	1
Package Length	13.0 in [33.0 cm]
Package Width	9.8 in [25.0 cm]
Package Height	0.6 in [14.0 mm]
Shipping (Package) Weight	5.7 oz [161.0 g]

What's in the



Box

Included in Package 1m External Serial Attached SCSI SAS Cable - SFF-8088 to SFF-8088

****Product appearance and specifications are subject to change without notice.***

