

2m External Mini SAS Cable - Serial Attached SCSI SFF-8088 to SFF-8088

Product ID: ISAS88882



The ISAS88882m External SAS Cable is designed for high-performance networks, servers, workstations and desktops, supporting data transfer rates of up to 6 Gbps.

This durable Mini SAS cable features SFF-8088 to SFF-8088 plugs for connecting your external SAS devices (controllers, hard drives, SAN storage area network, etc.), and it is TAA-compliant for Federal (GSA Schedule) purchases.

Constructed of high quality materials this 2-meter SAS cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- For use in Storage Area Networks, to connect SAS Expander enabled controllers and enclosures
- Connect SAS Controllers to SAS Backplanes
- Connect external hard drive to SAS Controller

Features

- 2x SFF-8088 plugs with latches
 - Durable metal connectors
 - Supports data transfer rates up to 6 Gbps
 - Multi-lane design
 - Backwards compatible with SATA devices
-

Hardware	Warranty	Lifetime
	Number of Conductors	8 Twisted Pair
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Cable Shield Material	Aluminum-polyester foil with tinned copper braid
Performance	Maximum Cable Length	6.6 ft [2 m]
Connector(s)	Connector A	SFF-8088 (26-pin, External Mini-SAS)
	Connector B	SFF-8088 (26-pin, External Mini-SAS)
Physical Characteristics	Color	Black
	Wire Gauge	28 AWG
	Cable Length	6.6 ft [2 m]
	Product Length	6.6 ft [2.0 m]
	Product Width	0.0 in [0.000 mm]
	Product Height	0.0 in [0.000 mm]
	Weight of Product	7.7 oz [218.000 g]
Packaging Information	Package Quantity	1
	Package Length	12.8 in [3.2 cm]
	Package Width	9.8 in [2.5 cm]
	Package Height	0.6 in [15.000 mm]
	Shipping (Package) Weight	8.3 oz [236.000 g]
What's in the Box	Included in Package	2m External Serial Attached SCSI SAS Cable - SFF-8088 to SFF-8088

**Product appearance and specifications are subject to change without notice.*

