

3m External Mini SAS Cable - Serial Attached SCSI SFF-8088 to SFF-8088 - TAA

Product ID: ISAS88883



The ISAS88883 3m External SAS Cable is designed for high-performance networks, servers, workstations and desktops, supporting data transfer rates of up to 6 Gbps.

This durable Mini SAS cable features SFF-8088 to SFF-8088 plugs for connecting your external SAS devices (controllers, hard drives, SAN storage area network, etc.), and it is TAA-compliant for Federal (GSA Schedule) purchases.

Constructed of high quality materials this 3-meter SAS cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- For use in Storage Area Networks, to connect SAS Expander enabled controllers and enclosures
- Connect SAS Controllers to SAS Backplanes
- Connect external hard drive to SAS Controller

Features

- 2x SFF-8088 plugs with latches

- Durable metal connectors
- Supports data transfer rates up to 6 Gbps
- Multi-lane design
- Backwards compatible with SATA devices

Hardware

Warranty	Lifetime
Number of Conductors	8 Twisted Pair
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-polyester foil with tinned copper braid

Connector(s)

Connector A	1 - SFF-8088 (26-pin, External Mini-SAS)
Connector B	1 - SFF-8088 (26-pin, External Mini-SAS)

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	9.8 ft [3 m]
Product Length	9.8 ft [3.0 m]
Product Width	1.4 in [3.5 cm]
Product Height	0.6 in [1.5 cm]
Weight of Product	10.9 oz [310.0 g]

Packaging Information

Package Quantity	1
Package Length	13.0 in [33.0 cm]
Package Width	10.0 in [25.5 cm]
Package Height	1.0 in [2.5 cm]

Shipping (Package) Weight	10.9 oz [310.0 g]
------------------------------	-------------------

What's in the Box

Included in Package	1 - 3m External Serial Attached SCSI SAS Cable - SFF-8088 to SFF-8088
---------------------	---

****Product appearance and specifications are subject to change without notice.***