

## Universal DC Power Adapter for Industrial USB Hubs - 20V, 3.25A

### Product ID: ITB20D3250

This universal DC power adapter has been designed as an alternative, back up or replacement power supply for StarTech.com's line of industrial USB hubs.

10-Port Industrial USB 3.0 Hub with External Power Adapter - ESD & 350W Surge Protection (HB30A10AME)

10-Port Industrial USB 3.0 Hub with ESD & 350W Surge Protection (ST1030USBM)

7-Port Industrial USB 3.0 Hub with External Power Adapter - ESD & 350W Surge Protection (HB30A7AME)

7-Port Industrial USB 3.0 Hub with ESD & 350W Surge Protection (ST7300USBME)

4-Port Industrial USB 3.0 Hub with ESD Protection (ST4300USBM)

7-Port Industrial USB 2.0 Hub ESD Protection & 350W Surge Protection (HB20A7AME)

7-Port Industrial USB 2.0 Hub with ESD & 350W Surge Protection (ST7200USBM)

4-Port Industrial USB 2.0 Hub with ESD Protection & 350W Surge Protection (HB20A4AME)

4-Port Industrial USB 2.0 Hub with ESD Protection (ST4200USBM)

The external terminal power adapter can also be used with any other devices that can support 20V power supply including a variety of StarTech.com Ethernet Switches and Serial Adapters.

The ITB20D3250 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

## Applications

## Features

- Terminal block power adapter has been designed for StarTech.com industrial products
- Use as an alternative power source, replacement, or back-up power supply when sufficient bus-power is unavailable
- Includes regional plug attachments for NA/JP, EU, UK & ANZ
- Includes an attached two conductor terminal block
- Includes an additional three conductor terminal block

---

### Indicators

Warranty

1 Year

LED Indicators                      Green Power LED

---

**Power**

|                              |  |
|------------------------------|--|
| Input Voltage                | 110V-240V AC                                       |
| Input Current                | 1.4A Max.  |
| Output Voltage               | 20V DC   |
| Output Current               | 3.25A  |
| Plug Type                    | Terminal Block (2 Wire)<br>Terminal Block (3 Wire) |
| Power Consumption (In Watts) | 65W  |

---

**Environmental**

|                       |                  |
|-----------------------|------------------|
| Operating Temperature | + 0°C ~ + 40°C   |
| Storage Temperature   | - 20 °C ~ + 80°C |
| Humidity              | 20% ~ 80% RH     |

---

**Physical Characteristics**

|                   |                   |
|-------------------|-------------------|
| Color             | Black             |
| Cable Length      | 6.0 ft [1.8 m]    |
| Product Length    | 4.5 in [11.5 cm]  |
| Product Width     | 2.1 in [53.0 mm]  |
| Product Height    | 1.5 in [37.0 mm]  |
| Weight of Product | 10.3 oz [291.0 g] |

---

**Packaging Information**

|                    |                   |
|--------------------|-------------------|
| Package Length     | 6.5 in [16.6 cm]  |
| Package Width      | 9.5 in [24.2 cm]  |
| Package Height     | 2.2 in [55.0 mm]  |
| Shipping (Package) | 29.8 oz [843.0 g] |



Weight

---

**What's in the  
Box**

|                     |   |
|---------------------|---|
| Included in Package | Universal 65W Power Adapter with 6ft [1.8m] Cable |
|                     | 5ft [1.5m] Power Cords (NA/JP, EU, UK, ANZ)       |
|                     | Two Conductor Terminal Block Connector (Attached) |
|                     | Three Conductor Terminal Block Connector          |
|                     | Quick-Start Guide                                 |

---

***\*Product appearance and specifications are subject to change without notice.***

