

HPE J9152A Compatible SFP+ Module - 10GBASE-LRM - 10GbE Multi Mode Fiber Optic Transceiver - 10GE Gigabit Ethernet SFP+ - LC 200m - 1310nm - DDM HPE 1850, 2540, 2930M  
Product ID: J9152A-ST



The J9152A-ST is a HP J9152A compatible fiber transceiver module that has been designed, programmed and tested to work with HP brand switches and routers. It delivers dependable 10 GbE connectivity over fiber cable, for 10GBase-LRM compliant networks, with a maximum distance of up to 200 m (656 ft).

- 1310nm
- 10 Gbps
- Multi Mode Fiber
- LC Connector
- 200 m (656 ft)
- 145,858,878 hours
- < 1W
- Yes

This SFP+ fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

## Certifications, Reports and Compatibility



## Applications

### Features

- 100% HPE J9152A COMPATIBLE: Works with HPE switches like 1850, 2540, 2930M, 3500yl, 3800 and others
- TECHNICAL SPECS: 10GBASE-LRM 10Gbps Multi Mode (MMF) LC Connector 1310nm Digital Diagnostic Monitoring (DDM) Distances up to 200m (656ft)

- **TESTED FOR OEM HOST COMPATIBILITY:** Hot-swappable in HPE routers and switches; DDM support reports the transceiver's status to most SNMP network management tools
- **LIFETIME WARRANTY:** Backed by a lifetime warranty on the life of the module itself - not the life of your switch. Our modules won't void your OEM warranty and supported by our Tech Advisors 5/24
- **WORKS WITH MSA COMPLIANT SWITCHES:** Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules

<b>Hardware</b>	Warranty	Lifetime
	Compatible Brand	HPE
	Industry Standards	IEEE 802.3aq 10GBASE-LRM
<b>Performance</b>	Maximum Data Transfer Rate	10.31 Gbps
	Max Transfer Distance	200 m (656 ft)
	Type	Multi Mode
	Wavelength	1310nm
	Fiber Operating Mode	Full-Duplex
	DDM	Yes
	Compatible Networks	10 Gbps
	MTBF	145,858,878 hours
	Power Consumption (In Watts)	< 1W
<b>Physical Characteristics</b>	Product Length	0.5 in [13.900 mm]
	Product Width	2.3 in [58.4 mm]
	Product Height	0.5 in [13.7 mm]
	Weight of Product	0.7 oz [21 g]
<b>Packaging Information</b>	Package Length	4.5 in [1.2 cm]
	Package Width	3.5 in [90 mm]
	Package Height	1.2 in [31 mm]
	Shipping (Package) Weight	1.8 oz [50 g]
<b>What's in the Box</b>	Included in Package	SFP+ Transceiver

*\*Product appearance and specifications are subject to change without notice.*