

HP J9152A Compatible SFP+ Transceiver Module - 10GBASE-LRM

Product ID: J9152AST



The J9152AST is an HP J9152A compatible fiber transceiver module that has been designed, programmed and tested to work with HP brand switches and routers. It delivers dependable 10 GbE connectivity over fiber cable, for 10GBASE-LRM compliant networks, with a maximum distance of up to 220 m (721 ft).

- 1310 nm
- 10 Gbps
- Multi Mode Fiber
- LC Connector
- 220 m (721 ft)
- 1,535,075 hours
- Less than 1.2 Watts
- Yes

This SFP+ fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility



Applications

- Replacing defective or damaged SFP+ modules in HP switches and routers
- Expand your network to remote segments

Features

- 100% compatibility with HP J9152A guaranteed
- StarTech.com SFP modules are backed by a lifetime warranty

- Meets or exceeds OEM specifications and Multi-Source Agreement (MSA) industry standards
- Low power consumption of less than 1 W
- Hot-swappable with fiber-optic modules

Hardware	Warranty	90 Days
	Compatible Brand	HPE
	Industry Standards	IEEE 802.3aq 10GBASE-LRM
Performance	Maximum Data Transfer Rate	10 Gbps
	Max Transfer Distance	220 m (721 ft.)
	Type	Multi Mode
	Wavelength	1310nm
	Fiber Operating Mode	Full-Duplex
	DDM	Yes
	Compatible Networks	10 Gbps
	MTBF	1,535,075 hours
	Power Consumption (In Watts)	< 1 W
Connector(s)	Local Unit Connectors	Fiber Optic LC Duplex
Special Notes / Requirements	Note	For use in 10 Gigabit fiber networking equipment and media converters
Environmental	Operating Temperature	0C to 70C (32F to 158F)
	Storage Temperature	-40C to 85C (-40F to 185F)
	Humidity	5~95% RH
Physical Characteristics	Product Length	2.3 in [58.400 mm]
	Product Width	0.5 in [13.900 mm]
	Product Height	0.5 in [12.600 mm]
	Weight of Product	0.7 oz [20.000 g]
Packaging Information	Package Length	3.7 in [93.000 mm]
	Package Width	4.6 in [11.8 cm]
	Package Height	1.4 in [35.000 mm]
	Shipping (Package)	1.8 oz [52.000 g]

Weight

What's in the Box	Included in Package	SFP+ transceiver
--------------------------	---------------------	------------------

**Product appearance and specifications are subject to change without notice.*

