

HPE JD089B Compatible SFP Module - 1000BASE-T - SFP to RJ45 Cat6/Cat5e - 1GE Gigabit Ethernet SFP - RJ-45 100m - HPE 5820AF, 12500, 5500

Product ID: JD089BST



The JD089BST is an HP JD089B compatible copper transceiver module that has been designed, programmed and tested to work with HP brand switches and routers. It delivers dependable 1 GbE connectivity over fiber cable, for 1000BASE-T compliant networks, with a maximum distance of up to 100 m (328 ft).

- 1000 Mbps
- Copper
- RJ45 Connector
- 100 m (328 ft)
- 4,655,371 hours
- Less than 1.3 Watts
- No

This SFP copper module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility



Applications

- Replacing defective or damaged SFP modules in HP switches and routers
- Expand your network to remote segments

Features

- 100% HPE JD089B COMPATIBLE: Works with HPE switches like 5820AF, 12500, 5500, E4800, E4500 and others

- TECHNICAL SPECS: 1000BASE-T 1Gbps Copper RJ-45 Connector Distances up to 100m (328ft)
- TESTED FOR OEM HOST COMPATIBILITY: Hot-swappable in HPE routers and switches
- LIFETIME WARRANTY: Backed by a lifetime warranty on the life of the module itself - not the life of your switch. Our modules won't void your OEM warranty and supported by our Tech Advisors 5/24
- WORKS WITH MSA COMPLIANT SWITCHES: Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules

Hardware	Warranty	Lifetime
	Compatible Brand	HPE
	Industry Standards	IEEE 802.3ab 1000BASE-T
	Industry Standards	IEEE 802.3i 10BASE-T
	Industry Standards	IEEE 802.3u 100BASE-TX
Performance	Maximum Data Transfer Rate	1000 Mbps
	Max Transfer Distance	100 m (328 ft)
	Type	Copper
	Fiber Operating Mode	Full-Duplex
	DDM	No
	Compatible Networks	10/100/1000 Mbps
	MTBF	4,655,371 hours
	Power Consumption (In Watts)	< 1.3 W
Connector(s)	Local Unit Connectors	RJ-45
Environmental	Operating Temperature	0C to 70C (32F to 158F)
	Storage Temperature	-40C to 85C (-40F to 185F)
	Humidity	5~95% RH
Physical Characteristics	Product Length	2.7 in [68 mm]
	Product Width	0.5 in [13.7 mm]
	Product Height	0.5 in [13.8 mm]
	Weight of Product	0.9 oz [25 g]
Packaging Information	Package Length	3.7 in [93 mm]
	Package Width	4.7 in [1.2 cm]
	Package Height	1.4 in [35 mm]

Shipping (Package) Weight	1.9 oz [54 g]
------------------------------	---------------

What's in the Box	Included in Package	SFP transceiver
------------------------------	---------------------	-----------------

****Product appearance and specifications are subject to change without notice.***

