

## HPE JD094B-BX-U Compatible SFP+ Module - 10GBASE-BX - 10 GbE Gigabit Ethernet BiDi Fiber (SMF) (JD094B-BX-U-ST)

**Product ID:** JD094B-BX-U-ST



The JD094B-BX-U-ST is an HP JD094B-BX-U compatible upstream fiber SFP+ transceiver which pairs with StarTech.com's JD094B-BX-D-ST. They are designed, programmed and tested to work with 10GBase-BX compatible HP switches and routers. The SFP+ transceiver module supports a maximum distance of up to 10 km (6.2 mi) and delivers dependable 10 GbE connectivity over fiber cabling.

### Technical Specifications:

- Wavelength: 1270nmTx/1330nmRx
- Maximum Data Transfer Rate: 10Gbps
- Type: Single Mode Fiber
- Connection Type: LC Connector
- Maximum Transfer Distance: 10 km (6.2 mi)
- Power Consumption: < 1.3W
- DDM: Yes

This SFP+ fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP+ modules and direct-attach SFP+ Cables, providing the convenience and reliability you need to ensure dependable network performance.

## Certifications, Reports and Compatibility

## Applications

## Features

- **100% HPE JD094B-BX-U COMPATIBLE:** 10 Gigabit Ethernet BiDi Fiber Single Strand SFP+ works with HPE switches like 5900, 12500, 5500, 5820, 5120 and others
- **INCREASE BANDWIDTH ON EXISTING INFRASTRUCTURE:** This 10 Gigabit Ethernet bi-directional WDM SFP+ transceiver module sends and receives over a single strand of fiber optic cable instead of two
- **TECHNICAL SPECS:** 10GBASE-BX 10Gbps 10G Bi-Directional Upstream Single Mode (SMF) LC Connector 1270nmTx/1330nmRx Digital Diagnostic Monitoring (DDM) Distances up to 10km (6.2mi)
- **LIFETIME WARRANTY:** Backed by a lifetime warranty on the life of the module itself, not the life of your switch. Our modules won't void your OEM warranty and supported by our Tech Advisors 5/24
- **PROGRAMMED & TESTED FOR COMPATIBILITY:** Compatible with OEM routers and switches. MSA Compliant with DDM that reports the transceiver's status to most SNMP network management tools

---

### Hardware

Warranty	Lifetime
Compatible Brand	HPE
Industry Standards	IEEE 802.3ae 10GBASE-BX

---

### Performance

Maximum Data Transfer Rate	10.00 Gbps
Max Transfer Distance	10 km (6.2 mi)
Type	Single Mode
Wavelength	1270nmTx/1330nmRx
Fiber Operating Mode	Full-Duplex
DDM	Yes
Compatible Networks	10 Gbps
MTBF	646,156,559 hours
Power Consumption (In Watts)	< 1.3W



---

**Physical  
Characteristics**

Product Length	0.5 in [13.9 mm]
Product Width	2.3 in [58.4 mm]
Product Height	0.5 in [12.6 mm]
Weight of Product	0.8 oz [24 g]

---

**Packaging  
Information**

Package Length	4.5 in [11.5 cm]
Package Width	3.5 in [90 mm]
Package Height	1.2 in [31 mm]
Shipping (Package) Weight	1.8 oz [50 g]

---

**What's in the Box**

Included in Package	SFP+ Transceiver
---------------------	------------------

---

***\*Product appearance and specifications are subject to change without notice.***

