

6in (15cm) Heavy Duty Power Cord, NEMA L5-20P to NEMA 5-20R, Black Adapter Cord, 20A 125V, 12AWG, Heavy Gauge Plug Converter Cable, TAA Compliant, UL Listed

Produkt-ID: K31D-2U00-POWER-CORD



The IT Pro's Choice

StarTech.com's power cables are designed by IT professionals. We design our products to meet the technical requirements of wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Reduced environmental impact and safe disposal by adhering to the rules, regulations, and directives stipulated by REACH and RoHS
- 100% Copper wiring tested for continuity and conductivity, ensuring maximum performance and reliability
- Temperature chamber tested to ensure reliable performance across a range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Heavy Duty power cord supports high-powered equipment and PDUs
- Extend a server or rackmount equipment power cord by an additional 6in

Merkmale

- **HEAVY DUTY ADAPTER CABLE:** 6in heavy gauge power cord with NEMA L5-20P to NEMA 5-20R connector is suitable for high-powered equipment; Convert a NEMA L5-20 outlet for high-power devices requiring a NEMA 5-20R connection; Indoor use; Rated up to 125V at 20A
- **BUILT FOR PERFORMANCE AND SAFETY:** UL Listed; VW-1 Fire Rated cable with fully molded connector strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- **SPECS:** 6in (15.24cm); TAA Compliant; NEMA L5-20P to NEMA 5-20R; 12AWG; 125V 20A (Max); Jacket Rating: SJT; Color: Black; Temperature Range: -4°F to 221°F (-20 to 105); Cable O.D.: 0.44in (11.2mm)
- **COMPATIBILITY:** NEMA L5-20P to NEMA 5-20R adapter power cord works with North American PDUs and high-powered devices; Convert an L5-20 outlet to NEMA 5-20R for convenient integration with servers, switches, or UPS; Heavy duty adapter power cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this heavy duty adapter power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance; This adapter power cable is available in other plug configurations

Hardware

Garantiebestimmungen	Lifetime
Anzahl von Leitern	3
Steckverbinderplatten	Nickel
Typ der Kabelummantelung	PVC
Feuerwiderstandssklasse	Klasse VW-1 e

	Kabeltyp	SJT
<hr/>		
Steckverbinder		
	Steckverbinder A	1 - NEMA L5-20P (North America)
	Steckverbinder B	1 - NEMA 5-20R (North America)
<hr/>		
Strom		
	Eingangsspannung	125V AC
	Eingangsstrom	20A
<hr/>		
Umgebungsbedingungen		
	Betriebstemperatur	-20° to 105°C (-4° to 221°F)
	Lagertemperatur	-20° to 105°C (-4° to 221°F)
	Feuchtigkeit	0% to 65% RH
<hr/>		
Physische Eigenschaften		
	Farbe	Schwarz
	Drahtstärke	12 AWG
	Kabellänge	6.0 in [15.2 cm]
	Außendurchmesser des Kabels	0.4 in [11.2 mm]
	Produktlänge	6.7 in [17.0 cm]
	Produktbreite	1.6 in [4.0 cm]
	Produkthöhe	1.4 in [3.5 cm]
	Produktgewicht	5.9 oz [166.0 g]
<hr/>		
Verpackungsinformationen		
	Paketlänge	9.9 in [25.1 cm]
	Paketbreite	2.7 in [6.8 cm]

Pakethöhe	1.7 in [4.2 cm]
Versandgewicht (Verpackung)	6.4 oz [180.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - 15cm NEMA L5-20P auf NEMA 5-20R Robustes Netzkabel
--------------------	---

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.