

## 10 ft Cat5e Blue Molded Crossover RJ45 UTP Cat5e Patch Cable - 10ft Patch Cord

Productcode: M45CROSS10BL



StarTech.com's Cat5e UTP Crossover Patch Cables offer reliable Ethernet connections. This 10ft cable meets or exceeds all Category 5e specifications and features a durable blue jacket that simplifies departmental color coding, while providing rugged flexibility for network connections.

To ensure long-lasting performance, our high quality Cat5e UTP Crossover Patch Cables offer PVC molded strain relief that prevents the RJ45 connector termination point from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

StarTech.com's 10ft blue Cat 5e UTP Crossover Patch Cable is constructed of only top quality materials to ensure optimum durability and is backed by StarTech.com's Lifetime Warranty.

StarTech.com Cat 5e cables are manufactured with copper conductors. While many cable manufacturers offer a "cheaper" cable based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value for your cable investment.

Our Cat 5 cables are constructed with 24 gauge copper wire to support a broad range of Ethernet applications, such as Power over Ethernet (PoE). Because we use a high quality 24 gauge wire, our cables easily sustain the nominal voltage (48v) capability required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat build up, equipment damage and potentially, fire.

StarTech.com Cat 5 cables offer high quality connectors comprised of 50 micron gold to ensure optimum conductivity while eliminating signal loss due to oxidation or corrosion.

### Certificaties, rapporten en compatibiliteit



## Toepassingen

- Connects workstation to workstation
- Patches from hub to hub

## Eigenschappen

- StarTech Category 5e Patch cables are constructed of top quality components
- The Strain relief prevents the cable from being bent at sharp angles at the connector to minimize the stress at the plug termination point
- Coloured Hoods for departmental colour coding
- StarTech Category 5e patch cables are carefully constructed and tested, to keep the Near End Crosstalk (NEXT) well within acceptable limits

---

### Hardware

Garantiebeleid	Lifetime
Aantal geleiders	4 pair UTP
Type kabelmantel	PVC - Polyvinyl Chloride
Brandbestendigheid	CMG goedgekeurd (algemeen doel)
Type kabel	Crossover Gegoten
Kabelstandaard	TIA/EIA-568-B.1-2001 T568B

---

### Prestaties

Kabelspecificatie	CAT5e - 350 MHz
-------------------	-----------------

---

### Connector(en)

Connector A	RJ-45
Connector B	RJ-45

---

### Fysieke eigenschappen

Kleur	Blauw
Draaddikte	24 AWG



Type geleider	Gevlochten koper
Kabellengte	10.0 ft [3.0 m]
Lengte product	10.0 ft [3.0 m]

---

Verpakkingsinformatie

Package Length	7.7 in [19.6 cm]
Package Width	0.7 in [17.6 mm]
Package Height	8.3 in [21.1 cm]
Verzendgewicht (verpakt)	4.2 oz [120 g]

---

Wat wordt er meegeleverd

Meegeleverd	10 Ft Blue Molded Cross Patch Cable
-------------	-------------------------------------

---

\* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.

