

35 ft Cat5e Blue Molded Crossover RJ45 UTP Cat5e Patch Cable - 35ft Patch Cord

Productcode: M45CROSS35BL



StarTech.com's Cat5e UTP Crossover Patch Cables offer reliable Ethernet connections, with PVC molded strain relief that prevents the RJ45 connector termination point from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance

This 35ft (blue) Cat 5e UTP Crossover Patch Cable is constructed of only top quality materials (100% copper conductors, 24 gauge wire, 50 micron gold connectors) to ensure optimum performance and is backed by StarTech.com's Lifetime Warranty.

Certificaties, rapporten en compatibiliteit

Toepassingen

- Connects workstation to workstation
- Patches from hub to hub

Eigenschappen

- StarTech Category 5e Patch cables are constructed of top quality components
- The Strain relief prevents the cable from being bent at sharp angles at the connector to minimize the stress at the plug termination point
- Coloured Hoods for departmental colour coding

- StarTech Category 5e patch cables are carefully constructed and tested, to keep the Near End Crosstalk (NEXT) well within acceptable limits

Hardware

Garantiebeleid	Lifetime
Aantal geleiders	4 pair UTP
Type kabelmantel	PVC - Polyvinyl Chloride
Brandbestendigheid	CMG goedgekeurd (algemeen doel)
Type kabel	Crossover Gegoten
Kabelstandaard	TIA/EIA-568-B.1-2001 T568B

Prestaties

Kabelspecificatie	CAT5e - 350 MHz
-------------------	-----------------

Connector(en)

Connector A	RJ-45
Connector B	RJ-45

Fysieke eigenschappen

Kleur	Blauw
Draaddikte	24 AWG
Type geleider	Gevlochten koper
Kabellengte	35.0 ft [10.7 m]
Lengte product	35.0 ft [10.7 m]

Verpakkingsinformatie

Package Length	10.0 in [25.5 cm]
Package Width	0.9 in [23.5 mm]
Package Height	12.7 in [32.2 cm]
Verzendgewicht	13.8 oz [390 g]



(verpakt)

Wat wordt er
meegeleverd

Meegeleverd

35 FOOT BLUE MOLDED CROSS PATCH CABLE

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.

