

75 ft Cat5e Blue Molded Crossover RJ45 UTP Cat5e Patch Cable - 75ft Patch Cord

Product ID: M45CROSS75BL



StarTech.com's Cat5e UTP Crossover Patch Cables offer reliable Ethernet connections, with PVC molded strain relief that prevents the RJ45 connector termination point from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance

This 75ft (blue) Cat 5e UTP Crossover Patch Cable is constructed of only top quality materials (100% copper conductors, 24 gauge wire, 50 micron gold connectors) to ensure optimum performance and is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Connects workstation to workstation
- Patches from hub to hub

Features

- StarTech Category 5e Patch cables are constructed of top quality components
 - The Strain relief prevents the cable from being bent at sharp angles at the connector to minimize the stress at the plug termination point
 - Coloured Hoods for departmental colour coding
-

Hardware

Warranty	Lifetime
Number of Conductors	4 pair UTP
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	CMG Rated (General Purpose)
Cable Type	Crossover Molded
Wiring Standard	TIA/EIA-568-B.1-2001 T568B

Performance

Cable Rating	CAT5e - 350 MHz
--------------	-----------------

Connector(s)

Connector A	RJ-45
Connector B	RJ-45

Physical Characteristics

Color	Blue
Wire Gauge	24 AWG
Cable Length	75.0 ft [22.9 m]
Product Length	75.0 ft [22.9 m]

Packaging Information

Package Length	9.7 in [24.6 cm]
Package Width	1.3 in [32 mm]
Package Height	12.6 in [32 cm]
Shipping (Package) Weight	28.2 oz [800 g]

What's in the Box

Included in Package	75 FOOT BLUE MOLDED CROSS PATCH CABLE
---------------------	---------------------------------------

**Product appearance and specifications are subject to change without notice.*