

15m Cat5e Blue Molded RJ45 UTP Cat 5e Patch Cable - 15 m Patch Cord

Product ID: M45PAT15MBL



The M45PAT15MBL Cat5e Patch Cable (15m) meets or exceeds all Cat 5e specifications to ensure reliable Ethernet network connections, and features a durable blue PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat5e patch cable features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

Constructed of only top quality materials, this Cat5e Patch Cord delivers reliable performance and is backed by our Lifetime Warranty.

StarTech.com Cat5e cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable, based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat 5e cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

This molded patch cable offers high quality connectors comprised of 50-micron gold, to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

Certifications, Reports and Compatibility

Applications

- Connects workstation to wall outlet

- Patches from hub to distribution panel
- Designed for use with Fast Ethernet networks
- Extend the reach of your Ethernet network devices by 15m (49.2ft)

Features

- Molded RJ45 connectors
- Colored hoods for departmental color coding
- Constructed with top quality components
- Carefully constructed and tested, to keep Near End Crosstalk (NEXT) well within acceptable limits
- High quality 24AWG copper wire

Hardware

Warranty	Lifetime
Number of Conductors	4 Pair UTP
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	CMG Rated (General Purpose)
Cable Type	Molded
Wiring Standard	TIA/EIA-568-B.1-2001 T568B

Performance

Cable Rating	CAT5e - 350 MHz
--------------	-----------------

Connector(s)

Connector A	RJ-45
Connector B	RJ-45

Physical Characteristics

Color	Blue
Wire Gauge	24 AWG
Conductor Type	Stranded Copper



Cable Length	49.2 ft [15 m]
Product Length	49.2 ft [15 m]
Weight of Product	17.6 oz [498 g]

Packaging Information

Package Quantity	1
Package Length	13.0 in [33 cm]
Package Width	10.0 in [25.5 cm]
Package Height	1.2 in [30 mm]
Shipping (Package) Weight	18.4 oz [521 g]

What's in the Box

Included in Package	15 m Blue Molded Cat5e UTP Patch Cable
---------------------	--

****Product appearance and specifications are subject to change without notice.***

